




BNC AL 0,64

Industrial Connectors:Measuring and Testing Equipment:Measuring leads:0,64 mm system

Product description

Description	BNC adapter lead with insulated sockets for 0.64 mm round pillar and 0.64 mm rectangular pillar. Red inner lead, black shielding; cable type RG 58 A/U, 50 Ohm. For use with oscilloscopes, PC cards, etc
Type	BNC AL 0,64
Order No.	933 844-001
System	0.64 mm system
Cable length	120 cm BNC and 10 cm wire
Cable color	black
Housing Color	black

Drawing



Technical data

Pin dimensions	0.64 mm
Type of contact	socket
Type of termination	BNC, 2 x 0.64 mm diameter socket
Cable specification	highly flexible lead
Rated voltage	DC 60 V

Environmental conditions

Temperature range	-15 °C to +70 °C
-------------------	------------------