




MATERIAL NUMBER	OLD PART NUMBER	FINISHED LENGTH
1201140057	BTY6030-FBA	—

VOLTAGE RATING	10–30 VDC
AMPERAGE RATING PER PORT	4 AMPS
PROTECTION	IP67
OPERATING TEMPERATURE	–25°C TO 90°C
UL CERTIFICATIONS	UL RECOGNIZED, FILE NO. E46237
CSA CERTIFICATIONS	CSA CERTIFIED, FILE NO. LR6837

ITEM	COMPONENT	MATERIAL	FINISH
1	CONTACT SOCKET	COPPER ALLOY	GOLD OVER NICKEL
2	O–RING	VITON	RED
3	RECEPTACLE SHELL	BRASS	NICKEL PLATED
4	HOUSING	PBT	YELLOW
5	LABEL	ABS	WHITE
6	LENS	NYLON	CLEAR

ADDED BRK, REM/VD SHORT		DESCRIPTION REV	QUALITY SYMBOL ▽=0 ▽C=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE 1:25.4	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
EC NO: WEU2010-0463					mm	INCH	DRAWN BY DATE		TITLE MICRO-CHANGE MPIS 6 PORT PNP TWIN PORT 5P FIELD ATTACHABLE				
DRWN: LHARTMAN 2012/01/25				4 PLACES	±---	±---	LHARTMAN 2012/01/25						
CH'KD: TWOLDEGE				3 PLACES	±---	±---	CHECKED BY DATE		MOLEX INCORPORATED				
APPR: JFMURPHY				2 PLACES	±---	±.01	FPACHER 2010/03/23						
				1 PLACE	±0.3	±---	APPROVED BY DATE		DOCUMENT NO. SD-120114-078				
				ANGULAR ±---°			-----						
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			MATERIAL NO. SEE CHART		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				
							SIZE C						