

THIS DRAWING IS UNPUBLISHED

RELEASED FOR PUBLICATION

© COPYRIGHT

By

ALL RIGHTS RESERVED

LOC

AD

DIST

00

REVISIONS

P

LIF

DESCRIPTION

DA

DWRN

	APV
--	-----




U2

REVISÉ PER ECO-11-00458

11M

RK

HM



1. MATERIAL-HOUSING: PBT, UL94V-O RATED, COLOR- BLACK
CONTACTS: COPPER ALLOY PER ASTM B103
2. AMP TRADEMARK (EITHER SIDE).
3. 0.00076[.000030] MIN. GOLD IN CONTACT AREA, 0.00127-0.00254[.000050-.000100] TIN-LEAD IN AREA E,
ALL OVER 0.00127[.000050] MIN. NICKEL.
4. 0.00076[.000030] MIN. GOLD IN CONTACT AREA, 0.00127 - 0.00254 [.000050 - .000100]
TIN IN AREA E, ALL OVER 0.00127[.000050] MIN. NICKEL.
5. USE WITH 22-26 AWG WIRE SIZE, 1.27[.050] MAX INSULATION DIA., 0.381[.015] MAX INSULATION WALL THICKNESS.
6. CONTACT IDENTIFICATION NUMBER "2" LOCATED IN THIS AREA.
7. MOLDED CIRCUIT #1 IDENTIFIER IN LOCATION SHOWN.
8. OBSOLETE PART NUMBER.
9. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

81.28 [3.200]	31	64		8-102398-0
76.20 [3.000]	29	60		7-102398-8
68.58 [2.700]	26	54		7-102398-5
63.50 [2.500]	24	50		7-102398-3
50.80 [2.000]	19	40		6-102398-8
43.18 [1.700]	16	34		6-102398-5
40.64 [1.600]	15	32		6-102398-4
38.10 [1.500]	14	30		6-102398-3
35.56 [1.400]	13	28		6-102398-2
33.02 [1.300]	12	26		6-102398-1
30.48 [1.200]	11	24		6-102398-0
27.94 [1.100]	10	22		5-102398-9
25.40 [1.000]	9	20		5-102398-8
22.86 [.900]	8	18		5-102398-7
20.32 [.800]	7	16		5-102398-6
17.78 [.700]	6	14		5-102398-5
15.24 [.600]	5	12		5-102398-4
12.70 [.500]	4	10		5-102398-3
10.16 [.400]	3	8		5-102398-2
7.62 [.300]	2	6		5-102398-1
B	A	NO OF POSN	FINISH	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG. NO. R BROWN	07MAY03	 TE Connectivity	
		DWG. NO. J MOSIER	07MAY03		
DIMENSIONS: mm [INCHES]	TOLERANCES, UNLESS OTHERWISE SPECIFIED:	APPLIC. SPEC. J MOSIER	NAME	AMPMODU MT, RECEPTACLE ASSEMBLY STANDARD—PRESSURE CONTACTS FOR 22–26 AWG WIRE SIZE	
	0 PL/C ± — 1 PL/C ± — 2 PL/C ± 0.1X[.005] 3 PL/C ± — 4 PL/C ± — ANGLES ± —	PRODUCT SPEC 108–25015 APPLICATION SPEC 114–25032	SIZE	CAGE CODE	DRAWING NO
MATERIAL 	FINISH SEE TABLE	WEIGHT —	A1	00779	C=102398
		CUSTOMER DRAWING	SCALE	4:1	SHEET 1 OF 1
			REV	U	