

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [19193-0091](#)
Status: **Active**
Overview: [VersaKrimp™ Terminals and Splices](#)
Description: [VersaKrimp™ Ring Tongue Terminal for 14-16 AWG Wire](#)

Documents:
[Drawing \(PDF\)](#) [Product Specification PS-19902-013 \(PDF\)](#)
[Product Specification PS-19902-011 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR18689
UL E32244

General

Product Family Ring and Spade Terminals
Series [19193](#)
Crimp Quality Equipment Yes
Mil-Spec N/A
Overview [VersaKrimp™ Terminals and Splices](#)
Product Name VersaKrimp™
Type Ring
UPC 800755049251

Physical

Barrel Type Closed - Brazed
Insulation None
Material - Plating Mating Tin
Net Weight 0.709/g
Packaging Type Bag
Stud Size 10 (M5)
Wire Size AWG 14, 16
Wire Size mm² 1.30 - 2.00

Material Info

Old Part Number BB-339-10

Reference - Drawing Numbers

Product Specification PS-19902-011, PS-19902-013
Sales Drawing BB-CD30101




image - Reference only

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[19193Series](#)

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
PremiumGrade™	0640030100
Hand Crimp Tool	
Crimp Head for the	0640070100
AT-200™ Pneumatic	
Hand Tool	