


COMBICON Plugs,
Pitch 5.0 or 5.08 mm



The standard COMBICON plugs have now been joined by variants for vertical plug-in direction:

1. MVSTBR 2,5...-ST(-5,08), conductor entry on the coded side of the plug.
2. MVSTBW 2,5...-ST(-5,08), conductor entry on the rippled side of the plug.

Vertical plugs can be placed immediately against neighboring walls and removed without squashing the connected lines.


Both plugs are also available with 2 to 24 positions and a 5.0 and 5.08 mm pitch. Alternatively, the plugs are also available with screw flange and 2 to 20 positions for vibration-resistant connection to headers with threaded flange.

The plugs can be coded by inserting the coding elements CP-MSTB. The coding elements CR-MSTB are inserted into the recesses in the corresponding header. The self-adhesive marker cards SK 5/3,8 or SK 5,08/3,8 are used for labelling (see page 210).

The combination possibilities for plug connectors are documented in the COMBICON cross-reference list on pages 82 to 85.

Articles printed in bold can be delivered at short notice.

Products with black or gray housing available on request.



MVSTBR 2,5/...-ST

Plug-in direction vertical to the conductor axis, connection point facing the **smooth** wall (R) of the header

Pitch 5.0 or 5.08						
(IEC)	rigid	flexible				
[mm ²]	solid	stranded	AWG	[A]	U	[V]
Connection data	0.2-2.5	0.2-2.5	24-12	12	250	
Further technical data see page 221.						

Note:

Only actuate COMBICON plug connectors when under no load condition. If for operating reasons small loads must be switched, experimental values are available on request.

Description		No. of positions	Dim. a [mm]	Type	Order No.	Pcs. Pkt.
Plugs, 5.0 mm pitch, color: green		2	5	MVSTBR 2,5/2-ST	17 92 01 6	50
		3	10	MVSTBR 2,5/3-ST	17 92 02 9	
		4	15	MVSTBR 2,5/4-ST	17 92 03 2	
		5	20	MVSTBR 2,5/5-ST	17 92 04 5	
		6	25	MVSTBR 2,5/6-ST	17 92 05 8	
		7	30	MVSTBR 2,5/7-ST	17 92 06 1	
		8	35	MVSTBR 2,5/8-ST	17 92 07 4	
		9	40	MVSTBR 2,5/9-ST	17 92 08 7	
		10	45	MVSTBR 2,5/10-ST	17 92 09 0	
		11	50	MVSTBR 2,5/11-ST	17 92 10 0	
		12	55	MVSTBR 2,5/12-ST	17 92 11 3	
		13	60	MVSTBR 2,5/13-ST	17 92 12 6	
		14	65	MVSTBR 2,5/14-ST	17 92 13 9	
		15	70	MVSTBR 2,5/15-ST	17 92 14 2	
		16	75	MVSTBR 2,5/16-ST	17 92 15 5	
		17	80	MVSTBR 2,5/17-ST	17 92 16 8	
		18	85	MVSTBR 2,5/18-ST	17 92 17 1	
		19	90	MVSTBR 2,5/19-ST	17 92 18 4	
		20	95	MVSTBR 2,5/20-ST	17 92 19 7	
Plugs, 5.08 mm pitch, color: green		21	100	MVSTBR 2,5/21-ST	17 92 20 7	50
		22	105	MVSTBR 2,5/22-ST	17 92 21 0	
		23	110	MVSTBR 2,5/23-ST	17 92 22 3	
		24	115	MVSTBR 2,5/24-ST	17 92 23 6	
		2	5.08	MVSTBR 2,5/2-ST-5,08	17 92 24 9	
		3	10.16	MVSTBR 2,5/3-ST-5,08	17 92 25 2	
		4	15.24	MVSTBR 2,5/4-ST-5,08	17 92 26 5	
		5	20.32	MVSTBR 2,5/5-ST-5,08	17 92 27 8	
		6	25.40	MVSTBR 2,5/6-ST-5,08	17 92 28 1	
		7	30.48	MVSTBR 2,5/7-ST-5,08	17 92 29 4	
		8	35.56	MVSTBR 2,5/8-ST-5,08	17 92 30 4	
		9	40.64	MVSTBR 2,5/9-ST-5,08	17 92 31 7	
		10	45.72	MVSTBR 2,5/10-ST-5,08	17 92 32 0	
		11	50.80	MVSTBR 2,5/11-ST-5,08	17 92 33 3	
		12	55.88	MVSTBR 2,5/12-ST-5,08	17 92 34 6	
		13	60.96	MVSTBR 2,5/13-ST-5,08	17 92 35 9	
		14	66.04	MVSTBR 2,5/14-ST-5,08	17 92 36 2	
		15	71.12	MVSTBR 2,5/15-ST-5,08	17 92 37 5	
		16	76.20	MVSTBR 2,5/16-ST-5,08	17 92 38 8	
		17	81.28	MVSTBR 2,5/17-ST-5,08	17 92 39 1	
		18	86.36	MVSTBR 2,5/18-ST-5,08	17 92 40 1	
		19	91.44	MVSTBR 2,5/19-ST-5,08	17 92 41 4	
		20	96.52	MVSTBR 2,5/20-ST-5,08	17 92 42 7	
		21	101.60	MVSTBR 2,5/21-ST-5,08	17 92 43 0	
		22	106.68	MVSTBR 2,5/22-ST-5,08	17 92 44 3	
		23	111.76	MVSTBR 2,5/23-ST-5,08	17 92 45 6	
		24	116.84	MVSTBR 2,5/24-ST-5,08	17 92 46 9	

Screwdriver SZS 0,6 x 3,5 see page 120.

