



FEATURES:

- Provides a fast and easy method to splice two cables together to increase cable length.

MATERIALS:

Jacks : Brass, Nickel Plated

Insulation: Polypropylene

RATINGS:

Operating Voltage: 5000 VDC

Operating Temperature: +55° C. (+131° F.) Max.

Current: 15 Amperes Max.

ORDERING INFORMATION: Model 1829-*

* = Color, Standard Colors: -0 Black, -2 Red

Sold in packages of ten.

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02"$ (.51 mm), .xxx = $\pm .005"$ (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA