

SPECIFICATION OF RH SERIES

APPLICATIONS

The RH type bead cores are mainly produced for the cable wire assemblers and MATV CATV makers.

* Internal and external computer data and power cables


ORDERING CODE

K5B RH 14.2 x 28.5 x 6.35
(1) (2) (3) (4) (5)

- (1) MATERIAL
- (2) PRODUCT CODE
- (3) A DIM.
- (4) B DIM.
- (5) C DIM.






SHAPE



DIMENSIONS & CHARACTERISTICS

UNIT:mm

NO.	ORDERING CODE	A	B	C
1	RH 2.5x4x0.8	2.50±0.15	4.00±0.30	0.80±0.15
2	RH 2.5x7x0.8	2.50±0.15	7.00±0.30	0.80±0.15
3	RH 2.5x12x1.3	2.50±0.15	12.00±0.40	1.30±0.15



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.






KING CORE ELECTRONICS INC.
Tel:886-3-4698855 Fax:886-3-4691395

No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan
E-mail:kc@mail.kingcore.com.tw Web Site:http://www.kingcore.com.tw

SPECIFICATION OF RH SERIES

NO.	ORDERING CODE	A	B	C
4	RH 3x3x1	3.00±0.15	3.00±0.20	1.00±0.15
5	RH 3x3x1.2	3.00±0.15	3.00±0.20	1.20±0.15
6	RH 3x4x1	3.00±0.15	4.00±0.30	1.00±0.15
7	RH 3x6x1	3.00±0.15	6.00±0.30	1.00±0.15
8	RH 3.4x11.2x1.1	3.40±0.15	11.20±0.40	1.10±0.15
9	RH 3.5x3.5x0.8	3.50±0.15	3.50±0.20	0.80±0.15
10	RH 3.5x3.5x1.2	3.50±0.15	3.50±0.20	1.20±0.15
11	RH 3.5x3.5x1.7	3.50±0.15	3.50±0.20	1.70±0.15
12	RH 3.5x3.5x1.8	3.50±0.15	3.50±0.20	1.80±0.15
13	RH 3.5x4x1	3.50±0.15	4.00±0.30	1.00±0.15
14	RH 3.5x4x1.2	3.50±0.15	4.00±0.30	1.20±0.15
15	RH 3.5x4x1.3	3.50±0.15	4.00±0.30	1.30±0.15
16	RH 3.5x4x1.5	3.50±0.15	4.00±0.30	1.50±0.15
17	RH 3.5x4.5x0.8	3.50±0.15	4.50±0.30	0.80±0.15
18	RH 3.5x4.7x0.8	3.50±0.15	4.70±0.30	0.80±0.15
19	RH 3.5x5x0.8	3.50±0.15	5.00±0.30	0.80±0.15
20	RH 3.5x5x1.2	3.50±0.15	5.00±0.30	1.20±0.15
21	RH 3.5x5x1.3	3.50±0.15	5.00±0.30	1.30±0.15
22	RH 3.5x5x1.5	3.50±0.15	5.00±0.30	1.50±0.15
23	RH 3.5x5x1.8	3.50±0.15	5.00±0.30	1.80±0.15
24	RH 3.5x6x0.8	3.50±0.15	6.00±0.30	0.80±0.15
25	RH 3.5x6x1	3.50±0.15	6.00±0.30	1.00±0.15
26	RH 3.5x6x1.2	3.50±0.15	6.00±0.30	1.20±0.15
27	RH 3.5x6x1.3	3.50±0.15	6.00±0.30	1.30±0.15
28	RH 3.5x6x1.5	3.50±0.15	6.00±0.30	1.50±0.15
29	RH 3.5x6x1.8	3.50±0.15	6.00±0.30	1.80±0.15
30	RH 3.5x7x1.2	3.50±0.15	7.00±0.30	1.20±0.15
31	RH 3.5x7.5x0.8	3.50±0.15	7.50±0.30	0.80±0.15
32	RH 3.5x8x0.8	3.50±0.15	8.00±0.30	0.80±0.15
33	RH 3.5x8x1	3.50±0.15	8.00±0.30	1.00±0.15
34	RH 3.5x9x0.8	3.50±0.15	9.00±0.30	0.80±0.15
35	RH 3.5x9x1.3	3.50±0.15	9.00±0.30	1.30±0.15
36	RH 3.5x9.5x0.8	3.50±0.15	9.50±0.30	0.80±0.15
37	RH 3.5x14x0.8	3.50±0.15	14.00±0.40	0.80±0.15



※Other sizes are available upon request.


※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



KING CORE ELECTRONICS INC.
Tel:886-3-4698855 Fax:886-3-4691395

No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan
E-mail:kc@mail.kingcore.com.tw Web Site:http://www.kingcore.com.tw

SPECIFICATION OF RH SERIES



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



KING CORE ELECTRONICS INC.

Tel:886-3-4698855


Fax:886-3-4691395

No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan

E-mail:kc@mail.kingcore.com.tw

Web Site: <http://www.kingcore.com.tw>

SPECIFICATION OF RH SERIES



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



KING CORE ELECTRONICS INC.

Tel:886-3-4698855


Fax:886-3-4691395

No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan

E-mail:kc@mail.kingcore.com.tw

Web Site: <http://www.kingcore.com.tw>

SPECIFICATION OF RH SERIES



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



KING CORE ELECTRONICS INC.

Tel:886-3-4698855

Fax:886-3-4691395












No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan

E-mail:kc@mail.kingcore.com.tw

Web Site: <http://www.kingcore.com.tw>

SPECIFICATION OF RH SERIES

NO.	ORDERING CODE	A	B	C
38	RH 4x4x1.5	4.00±0.20	4.00±0.30	1.50±0.15
39	RH 4x4x2	4.00±0.20	4.00±0.30	2.00±0.15
40	RH 4x5x1.5	4.00±0.20	5.00±0.30	1.50±0.15
41	RH 4x5x2	4.00±0.20	5.00±0.30	2.00±0.15
42	RH 4x5.5x1.5	4.00±0.20	5.50±0.30	1.50±0.15
43	RH 4x6x2	4.00±0.20	6.00±0.30	2.00±0.15
44	RH 4x7x2	4.00±0.20	7.00±0.30	2.00±0.15
45	RH 4x8x2	4.00±0.20	8.00±0.30	2.00±0.15
46	RH 4x10x1.5	4.00±0.20	10.00±0.40	1.50±0.15
47	RH 4x10x2	4.00±0.20	10.00±0.40	2.00±0.15
48	RH 4x12x2	4.00±0.20	12.00±0.40	2.00±0.15
49	RH 4x12.5x1.5	4.00±0.20	12.50±0.40	1.50±0.15
50	RH 4x15x2	4.00±0.20	15.00±0.40	2.00±0.15
51	RH 4x17x2	4.00±0.20	17.00±0.40	2.00±0.15
52	RH 4.5x4.8x2.5	4.50±0.20	4.80±0.30	2.50±0.15
53	RH 4.5x7x2.5	4.50±0.20	7.00±0.30	2.50±0.15
54	RH 4.5x12x2.6	4.50±0.20	12.00±0.40	2.60±0.15
55	RH 4.6x11x2	4.60±0.20	11.00±0.40	2.00±0.15
56	RH 4.83x6.35x2.29	4.83±0.20	6.35±0.30	2.29±0.15



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



KING CORE ELECTRONICS INC.

Tel: 886-3-4698855


Fax: 886-3-4691395

E-mail: kc@mail.kingcore.com.tw

Web Site: <http://www.kingcore.com.tw>

No.269, Nanfong Rd., Pingjhen City, Taoyuan County, Taiwan

SPECIFICATION OF RH SERIES



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



KING CORE ELECTRONICS INC.

Tel: 886-3-4698855

Fax: 886-3-4691395
















No. 269, Nanfong Rd., Pingjhen City, Taoyuan County, Taiwan

E-mail: kc@mail.kingcore.com.tw

Web Site: <http://www.kingcore.com.tw>

SPECIFICATION OF RH SERIES

NO.	ORDERING CODE	A	B	C
57	RH 5x5x2.3	5.00±0.20	5.00±0.30	2.30±0.15
58	RH 5x6.2x1.6	5.00±0.20	6.20±0.30	1.60±0.15
59	RH 5x6.35x1.5	5.00±0.20	6.35±0.30	1.50±0.15
60	RH 5x6.35x2.36	5.00±0.20	6.35±0.30	2.36±0.15
61	RH 5x10x2.3	5.00±0.20	10.00±0.40	2.30±0.15
62	RH 5x11x1.5	5.00±0.20	11.00±0.40	1.50±0.15
63	RH 5x12x2.15	5.00±0.20	12.00±0.40	2.15±0.15
64	RH 5x18x2.15	5.00±0.20	18.00±0.40	2.15±0.15
65	RH 5x20x1.5	5.00±0.20	20.00±0.50	1.50±0.15
66	RH 5.7x8x1.5	5.70±0.20	8.00±0.30	1.50±0.15



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only. King Core reserves the right to alter or revise the specifications without prior notification.



KING CORE ELECTRONICS INC.

Tel:886-3-4698855

Fax:886-3-4691395
















No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan

E-mail:kc@mail.kingcore.com.tw

Web Site:http://www.kingcore.com.tw

SPECIFICATION OF RH SERIES

NO.	ORDERING CODE	A	B	C
67	RH 6x10x3	6.00±0.20	10.00±0.40	3.00±0.20
68	RH 6x10x4	6.00±0.20	10.00±0.40	4.00±0.20
69	RH 6x12.8x4	6.00±0.20	12.80±0.40	4.00±0.20
70	RH 6x18x3.15	6.00±0.20	18.00±0.40	3.15±0.20
71	RH 6x25x3	6.00±0.20	25.00±0.60	3.00±0.20
72	RH 6.35x12.7x3.3	6.35±0.20	12.70±0.40	3.30±0.20
73	RH 6.35x15.8x3.3	6.35±0.20	15.80±0.40	3.30±0.20
74	RH 6.5x10x4.3	6.50±0.20	10.00±0.40	4.30±0.20
75	RH 6.5x11x4.3	6.50±0.20	11.00±0.40	4.30±0.20



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



KING CORE ELECTRONICS INC.

Tel:886-3-4698855

Fax:886-3-4691395








No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan

E-mail:kc@mail.kingcore.com.tw

Web Site:http://www.kingcore.com.tw

SPECIFICATION OF RH SERIES

NO.	ORDERING CODE	A	B	C
76	RH 7.5x7.5x2.4	7.50±0.20	7.50±0.30	2.40±0.15
77	RH 7.9x10x3	7.90±0.20	10.00±0.40	3.00±0.20
78	RH 7.9x12.8x4	7.90±0.20	12.80±0.40	4.00±0.20
79	RH 7.9x19x3	7.90±0.20	19.00±0.40	3.00±0.20



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.










KING CORE ELECTRONICS INC.
Tel:886-3-4698855 Fax:886-3-4691395

No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan
E-mail:kc@mail.kingcore.com.tw Web Site:http://www.kingcore.com.tw

SPECIFICATION OF RH SERIES

NO.	ORDERING CODE	A	B	C
80	RH 8x9x6	8.00±0.20	9.00±0.30	6.00±0.30
81	RH 8x9.8x6	8.00±0.20	9.80±0.30	6.00±0.30
82	RH 8x10x4	8.00±0.20	10.00±0.40	4.00±0.20
83	RH 8x10.06x3.18	8.00±0.20	10.06±0.40	3.18±0.20
84	RH 8x12x6	8.00±0.20	12.00±0.40	6.00±0.30
85	RH 8x16x5	8.00±0.20	16.00±0.40	5.00±0.25
86	RH 8x20x5	8.00±0.20	20.00±0.50	5.00±0.25



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.









KING CORE ELECTRONICS INC.
Tel:886-3-4698855 Fax:886-3-4691395

No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan
E-mail:kc@mail.kingcore.com.tw Web Site:http://www.kingcore.com.tw

SPECIFICATION OF RH SERIES


NO.	ORDERING CODE	A	B	C
87	RH 9x10x4.5	9.00±0.30	10.00±0.40	4.50±0.20
88	RH 9x16x5	9.00±0.30	16.00±0.40	5.00±0.25
89	RH 9.3x9.5x4.5	9.30±0.30	9.50±0.30	4.50±0.20
90	RH 9.3x11x5.8	9.30±0.30	11.00±0.40	5.80±0.25
91	RH 9.5x9.5x4.8	9.50±0.30	9.50±0.30	4.80±0.20
92	RH 9.5x9.5x5.2	9.50±0.30	9.50±0.30	5.20±0.25
93	RH 9.5x10x5.2	9.50±0.30	10.00±0.40	5.20±0.25
94	RH 9.5x10x5.8	9.50±0.30	10.00±0.40	5.80±0.25
95	RH 9.5x10.4x5	9.50±0.30	10.40±0.40	5.00±0.25
96	RH 9.5x12.7x4.8	9.50±0.30	12.70±0.40	4.80±0.20
97	RH 9.5x14.5x5	9.50±0.30	14.50±0.40	5.00±0.25
98	RH 9.5x15.88x5	9.50±0.30	15.88±0.40	5.00±0.25
99	RH 9.5x16x5	9.50±0.30	16.00±0.40	5.00±0.25
100	RH 9.5x19x5	9.50±0.30	19.00±0.40	5.00±0.25
101	RH 9.5x19.5x5	9.50±0.30	19.50±0.40	5.00±0.25
102	RH 9.52x15.88x5.08	9.52±0.30	15.88±0.40	5.08±0.25
103	RH 9.8x11.4x0.8	9.80±0.30	11.40±0.40	0.80±0.15
104	RH 9.8x13.5x6.7	9.80±0.30	13.50±0.40	6.70±0.30
105	RH 9.8x19.05x6.7	9.80±0.30	19.05±0.40	6.70±0.30
106	RH 9.8x25x3.8	9.80±0.30	25.00±0.60	3.80±0.30



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.

SPECIFICATION OF RH SERIES



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



KING CORE ELECTRONICS INC.

Tel: 886-3-4698855

Fax: 886-3-4691395









No. 269, Nanfong Rd., Pingjhen City, Taoyuan County, Taiwan

E-mail: kc@mail.kingcore.com.tw

Web Site: <http://www.kingcore.com.tw>

SPECIFICATION OF RH SERIES

NO.	ORDERING CODE	A	B	C
107	RH 10x10x5	10.00±0.30	10.00±0.40	5.00±0.25
108	RH 10x10x6	10.00±0.30	10.00±0.40	6.00±0.30
109	RH 10x10x7	10.00±0.30	10.00±0.40	7.00±0.30
110	RH 10x14x6	10.00±0.30	14.00±0.40	6.00±0.30
111	RH 10.5x20x5.5	10.50±0.30	20.00±0.50	5.50±0.25
112	RH 10.5x25x5.5	10.50±0.30	25.00±0.60	5.50±0.25



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.











KING CORE ELECTRONICS INC.
Tel:886-3-4698855 Fax:886-3-4691395

No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan
E-mail:kc@mail.kingcore.com.tw Web Site:http://www.kingcore.com.tw

SPECIFICATION OF RH SERIES

NO.	ORDERING CODE	A	B	C
113	RH 11x16x5	11.00±0.30	16.00±0.40	5.00±0.25
114	RH 11x18.5x5	11.00±0.30	18.50±0.40	5.00±0.25
115	RH 11x20x5	11.00±0.30	20.00±0.50	5.00±0.25
116	RH 11x25x5	11.00±0.30	25.00±0.60	5.00±0.25
117	RH 11.5x18.5x5	11.50±0.30	18.50±0.40	5.00±0.25
118	RH 11.5x20x4.3	11.50±0.30	20.00±0.50	4.30±0.20
119	RH 11.5x26x4.3	11.50±0.30	26.00±0.60	4.30±0.20
120	RH 11.8x15x7.3	11.80±0.30	15.00±0.40	7.30±0.30



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.















KING CORE ELECTRONICS INC.
Tel:886-3-4698855 Fax:886-3-4691395

No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan
E-mail:kc@mail.kingcore.com.tw Web Site:http://www.kingcore.com.tw

SPECIFICATION OF RH SERIES

NO.	ORDERING CODE	A	B	C
121	RH 12x12x7	12.00±0.30	12.00±0.40	7.00±0.30
122	RH 12x12x8.5	12.00±0.30	12.00±0.40	8.50±0.30
123	RH 12x15x5.6	12.00±0.30	15.00±0.40	5.60±0.25
124	RH 12x15x7	12.00±0.30	15.00±0.40	7.00±0.30
125	RH 12x15x8.5	12.00±0.30	15.00±0.40	8.50±0.30
126	RH 12x20x5.6	12.00±0.30	20.00±0.50	5.60±0.25
127	RH 12x20x7.3	12.00±0.30	20.00±0.50	7.30±0.30
128	RH 12x30x5.6	12.00±0.30	30.00±0.70	5.60±0.25
129	RH 12.2x23x7.9	12.20±0.30	23.00±0.50	7.90±0.30
130	RH 12.3x20x7	12.30±0.30	20.00±0.50	7.00±0.30
131	RH 12.32x25.4x4.88	12.32±0.30	25.40±0.60	4.88±0.20
132	RH 12.5x12.5x8	12.50±0.30	12.50±0.40	8.00±0.30
133	RH 12.5x15x5.2	12.50±0.30	15.00±0.40	5.20±0.25
134	RH 12.7x12.7x7.9	12.70±0.30	12.70±0.40	7.90±0.30



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



KING CORE ELECTRONICS INC.

Tel:886-3-4698855









Fax:886-3-4691395

E-mail:kc@mail.kingcore.com.tw

No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan

Web Site:http://www.kingcore.com.tw

SPECIFICATION OF RH SERIES



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.















KING CORE ELECTRONICS INC.
Tel:886-3-4698855 Fax:886-3-4691395

No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan
E-mail:kc@mail.kingcore.com.tw Web Site:http://www.kingcore.com.tw

SPECIFICATION OF RH SERIES




NO.	ORDERING CODE	A	B	C
135	RH 14x15x9	14.00±0.40	15.00±0.40	9.00±0.30
136	RH 14.2x15x6.35	14.20±0.40	15.00±0.40	6.35±0.30
137	RH 14.2x15x7	14.20±0.40	15.00±0.40	7.00±0.30
138	RH 14.2x15x8	14.20±0.40	15.00±0.40	8.00±0.30
139	RH 14.2x18x6.35	14.20±0.40	18.00±0.40	6.35±0.30
140	RH 14.2x23.5x7	14.20±0.40	23.50±0.50	7.00±0.30
141	RH 14.2x28.5x6.35	14.20±0.40	28.50±0.60	6.35±0.30
142	RH 14.2x28.5x7	14.20±0.40	28.50±0.60	7.00±0.30
143	RH 14.2x28.5x8	14.20±0.40	28.50±0.60	8.00±0.30
144	RH 14.99x19x6.99	14.99±0.40	19.00±0.40	6.99±0.30
145	RH 14.99x27.94x6.99	14.99±0.40	27.94±0.60	6.99±0.30



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.

SPECIFICATION OF RH SERIES



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



KING CORE ELECTRONICS INC.

Tel:886-3-4698855

Fax:886-3-4691395









No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan

E-mail:kc@mail.kingcore.com.tw

Web Site: <http://www.kingcore.com.tw>

SPECIFICATION OF RH SERIES

NO.	ORDERING CODE	A	B	C
146	RH 15.2x28.5x10.2	15.20±0.40	28.50±0.60	10.20±0.40
147	RH 15.25x17x9	15.25±0.40	17.00±0.40	9.00±0.30
148	RH 15.25x28x8	15.25±0.40	28.00±0.60	8.00±0.30
149	RH 15.65x28.57x6.99	15.65±0.40	28.57±0.60	6.99±0.30
150	RH 15.8x16x7.9	15.80±0.40	16.00±0.40	7.90±0.30
151	RH 15.88x28.57x7.87	15.88±0.40	28.57±0.60	7.87±0.30

















※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.

SPECIFICATION OF RH SERIES

NO.	ORDERING CODE	A	B	C
152	RH 16x16x8	16.00±0.40	16.00±0.40	8.00±0.30
153	RH 16x17x9	16.00±0.40	17.00±0.40	9.00±0.30
154	RH 16x17.5x4.3	16.00±0.40	17.50±0.40	4.30±0.20
155	RH 16x20x7	16.00±0.40	20.00±0.50	7.00±0.30
156	RH 16x20x9	16.00±0.40	20.00±0.50	9.00±0.30
157	RH 16x28x7	16.00±0.40	28.00±0.60	7.00±0.30
158	RH 16x28x9	16.00±0.40	28.00±0.60	9.00±0.30
159	RH 16x28x10	16.00±0.40	28.00±0.60	10.00±0.40
160	RH 16x28.5x9	16.00±0.40	28.50±0.60	9.00±0.30



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



KING CORE ELECTRONICS INC.

Tel:886-3-4698855

Fax:886-3-4691395













No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan

E-mail:kc@mail.kingcore.com.tw

Web Site:http://www.kingcore.com.tw

SPECIFICATION OF RH SERIES

NO.	ORDERING CODE	A	B	C
161	RH 17.07x25.4x8.76	17.07±0.40	25.40±0.60	8.76±0.30
162	RH 17.5x23.5x9.5	17.50±0.40	23.50±0.50	9.50±0.30
163	RH 17.5x28.5x8	17.50±0.40	28.50±0.60	8.00±0.30
164	RH 17.5x28.5x8.3	17.50±0.40	28.50±0.60	8.30±0.30
165	RH 17.5x28.5x9.5	17.50±0.40	28.50±0.60	9.50±0.30
166	RH 17.5x28.5x10.7	17.50±0.40	28.50±0.60	10.70±0.40
167	RH 17.5x35x9.5	17.50±0.40	35.00±0.80	9.50±0.30










※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.

SPECIFICATION OF RH SERIES

NO.	ORDERING CODE	A	B	C
168	RH 18x18x10	18.00±0.50	18.00±0.40	10.00±0.40
169	RH 18x28x10	18.00±0.50	28.00±0.60	10.00±0.40
170	RH 18x29x10	18.00±0.50	29.00±0.60	10.00±0.40
171	RH 18.67x25x10.16	18.67±0.50	25.00±0.60	10.16±0.40
172	RH 18.67x28.57x10.16	18.67±0.50	28.57±0.60	10.16±0.40







※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.

SPECIFICATION OF RH SERIES

NO.	ORDERING CODE	A	B	C
173	RH 19x29x13	19.00±0.50	29.00±0.60	13.00±0.40
174	RH 19x31.5x5.8	19.00±0.50	31.50±0.70	5.80±0.25
175	RH 19x35x5.8	19.00±0.50	35.00±0.80	5.80±0.25
176	RH 19x35x6.3	19.00±0.50	35.00±0.80	6.30±0.30




※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.

SPECIFICATION OF RH SERIES

NO.	ORDERING CODE	A	B	C
177	RH 20x28.25x14.5	20.00±0.60	28.25±0.60	14.50±0.50



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



KING CORE ELECTRONICS INC.

Tel:886-3-4698855

Fax:886-3-4691395



No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan

E-mail:kc@mail.kingcore.com.tw

Web Site: <http://www.kingcore.com.tw>

SPECIFICATION OF RH SERIES

NO.	ORDERING CODE	A	B	C
178	RH 25.91x28.57x12.83	25.91±0.60	28.57±0.60	12.83±0.40



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



KING CORE ELECTRONICS INC.

Tel:886-3-4698855

Fax:886-3-4691395




E-mail:kc@mail.kingcore.com.tw

No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan

Web Site:http://www.kingcore.com.tw

SPECIFICATION OF RH SERIES

NO.	ORDERING CODE	A	B	C
179	RH 28x28x16	28.00±0.60	28.00±0.60	16.00±0.50
180	RH 28.5x28.57x13.77	28.50±0.60	28.57±0.60	13.77±0.40



※Other sizes are available upon request.

※All the data listed in this catalogue are for reference only, King Core reserves the right to alter or revise the specifications without prior notification.



KING CORE ELECTRONICS INC.
Tel:886-3-4698855 Fax:886-3-4691395

No.269,Nanfong Rd.,Pingjhen City,Taoyuan County,Taiwan
E-mail:kc@mail.kingcore.com.tw Web Site:http://www.kingcore.com.tw