



HBL20405



SEHBL3



SAB34



HBL20424B



HBL20425B



H660A

Dimensions in Inches (mm)

### 30 Amp Hubbellock® Accessories

#### Receptacle Plates for FS/FD Box Mounting

Description	Catalog Number
Thermoplastic, wet and damp locations with cover "open", gray.	HBL7428WOG*
Thermoplastic, wet and damp locations with cover "open", yellow.	HBL7428WOY*
Thermoplastic, wet and damp locations with cover "open", red.	HBL7428WOR*
Cast aluminum, wet location only when cover "closed" and damp locations, lift cover plate.	HBL20405
Cast aluminum, wet location only when cover "closed" and damp locations, red finish.	HBL20446
302/304 stainless, single gang, smooth. NOT weatherproof.	SS737

Note: \*Features two #6-32 threaded inserts to back mount device to cover.

IP54

SUITABILITY

#### Switched Enclosure

Description	Catalog Number
Switched enclosure for use with 30A 3 pole 4 wire Hubbellock receptacle. Receptacle not included.	SEHBL3

Note: For more information on switched enclosures see page B-37.

#### Liquidtight Metallic Conduit Adapters (Not Shown)

Description	Catalog Number
Adapter for use with 1/2" NPT conduit fittings.	SAB12
Adapter for use with 3/4" NPT conduit fittings.	SAB34

#### Boots

Description	Catalog Number
"Mini" boot for Hubbellock connector body.	HBL20424B†
"Mini" boot for Hubbellock plug.	HBL20425B†

Note: †Not UL Listed or CSA Certified.

### 60 Amp Hubbellock® Accessories


#### Receptacle Box and Adapter Plates (Box requires one adapter)

Description	Catalog Number
Box, cast aluminum, only for 60A Hubbellock receptacles.	HBL26401
Straight adapter plate.	HBL26402
45° adapter plate.	HBL26404


Note: Straight or angle adapter plate must be used when mounting a 60A receptacle to HBL26401 box.  
Cannot be used with round flanged receptacles and inlets.

#### Kellems® Cable Grip


Description	Cord Diameter	Catalog Number
Cable grip.	.830"-1.000" (21.1-25.4)	H660A
Cable grip (not shown).	1.000"-1.140" (25.4-28.9)	H661A
Cable grip (not shown).	1.125"-1.328 (28.6-33.7)	H662A



HBL26401



HBL26402



HBL26404