

# FLKM 14-PA-SLC500/OUT

Order No.: 2293459



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2293459>

VARIOFACE front adapter, 2 x 8 channels can be connected, for Allen-Bradley SLC 500, 1746 OB16, OV16, OG16 and IG16

## Commercial data

|                          |                    |
|--------------------------|--------------------|
| EAN                      | 4017918108854      |
| Pack                     | 1 pcs.             |
| Customs tariff           | 85369010           |
| Weight/Piece             | 0.0577 KG          |
| Catalog page information | Page 192 (IF-2009) |

## Product notes

WEEE/RoHS-compliant since:  
06/04/2007



<http://www.download.phoenixcontact.com>  
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

## Technical data

### General

|                                 |                                                            |
|---------------------------------|------------------------------------------------------------|
| Nominal voltage $U_N$           | < 50 V AC                                                  |
|                                 | 60 V DC                                                    |
| Connection type, plug connector | Flat-ribbon cable plug connector in acc. with IEC 60603-13 |
| Number of plug connectors       | 2                                                          |

|                                         |                                          |
|-----------------------------------------|------------------------------------------|
| No. of positions, plug connector        | 14                                       |
| Number of positions                     | 14                                       |
| Ambient temperature (operation)         | -20 °C ... 50 °C                         |
| Ambient temperature (storage/transport) | -20 °C ... 70 °C                         |
| Mounting position                       | Any                                      |
| Standards/regulations                   | IEC 60664                                |
|                                         | DIN EN 50178                             |
|                                         | IEC 62103                                |
| Max. permissible current                | 1 A (per path)                           |
| Max. permissible total current          | 2 A (Per Byte, for supply via connector) |
| Pollution degree                        | 1                                        |
| Surge voltage category                  | II                                       |
| Supported controller                    | ALLEN-BRADLEY SLC 500                    |
| Supported I/O card                      | 1746 OB16                                |
|                                         | 1746 OG16                                |
|                                         | 1746 OV16                                |
|                                         | 1746 IG16                                |

#### Certificates / Approvals




Certification

CUL, GOST, UL

#### Diagrams/Drawings

Circuit diagram



Connection scheme FLKM 14-PA-SLC500/OUT

**Address**

PHOENIX CONTACT Deutschland GmbH  
Flachsmarktstr. 8  
32825 Blomberg, Germany  
Phone +49 5235 3 12000  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.de>



© 2010 Phoenix Contact  
Technical modifications reserved;