



Red Hybrid Displays

Device Type	Luminous Intensity per Segment or per Diode		typ V	@ IF mA	Key Features
	typ μ cd	@ IF mA			
TIL302	275	20	3.4	20	0.27 inch high numeric display with decimal point in 14-lead dual-in-line plastic package
TIL303	275	20	3.4	20	Same as TIL302 except right hand decimal point
TIL304	275	20	3.4	20	Polarity and overflow unit
TIL305	110	10	1.65	10	0.3 inch high alpha-numeric character display in 5 x 7 dot matrix. 14-pin dual-in-line package
TIL306	275	*	*	*	0.27 inch high numeric display with logic in 16-pin dual-in-line package. Logic includes decade counter, latch, current source driver, and decoder
TIL307	275	*	*	*	Same as TIL306 except right hand decimal point
TIL308	275	*	*	*	Same as TIL306 except logic chip does not include decade
TIL309	275	*	*	*	Same as TIL308 except right hand decimal point
TIL311	110	*	*	*	0.27 inch high hexadecimal display with integral logic in 14-pin dual-in-line package

* Contains Integral Logic