





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	G3	REVISED PER ECO-16-004800	10SEP2016	NK	MZ
	H	REVISED PER ECO-17-000037	10MAR2017	RS	MZ



(-1, -2, -4 & -5 ONLY)



(-3 ONLY)



4	OBSOLETE	STANDARD	-206837-5
4	OBSOLETE	STANDARD	-206837-4
		STANDARD	206837-3
		SMALL PACK	206837-2
		STANDARD	206837-1
		PACKAGING	PART NUMBER

- 1 CONNECTOR WILL ACCEPT (24) MULTIMATE SOCKET CONTACTS.
- 2 MAXIMUM INSULATION NOT TO EXCEED .150 DIA.
- 3 CONTACT CAVITIES IDENTIFIED BY CHARACTERS ON FRONT AND REAR FACE OF CONNECTOR.
- 4 WHITE DOT NEAR POSITION 1 ON WIRE ENTRY FACE.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL
SEE CALLOUT

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH -

DWN
S. RIDGLEY BG
31 JUL 90

CHK
R. STONE
26 APR 91

APVD
K. BEAVER
03 APR 91

PRODUCT SPEC
108-10024

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
PLUG ASSEMBLY, SHELL SIZE 23,
STANDARD SEX, SERIES 1, CPC

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=206837

RESTRICTED TO
-

SCALE
2:1

SHEET
1 OF 1

REV
H