

Technical data

Material	: Polypropylene (PP)
Adhesive material (for HTC-SK)	: Synthetic rubber with base of polyethylene foam
Colour	: White
Operating temperature	: From -20 °C to +70 °C
Flammability (excluding adhesive)	: UL94 V0
Approvals	: Material: UL94 V0 (File E86615)



Article-No.	Type	Inner Ø	Capacity in pieces (no. of wires)		
			0,75 mm²	1,5 mm²	2,5 mm²
<i>screwable</i>					
164-11008	Heladuct Flex10	9 x 11	9	6	4
164-21008	Heladuct Flex20	20	32	22	14
164-31008	Heladuct Flex30	30	67	50	34
164-41008	Heladuct Flex40	40	-	81	60
<i>adhesive</i>					
164-11108	Heladuct Flex10 SK	9 x 11	9	6	4
164-21108	Heladuct Flex20 SK	20	32	22	14
164-31108	Heladuct Flex30 SK	30	67	50	34
164-41108	Heladuct Flex40 SK	40	-	81	60

All dimensions in mm. Supplied in 500mm length.