

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

98268-0384

Status:

Active

Overview:

Premo-Flex™ FFC and Etched Polyimide Jumpers

Description:

1.25mm Pitch Premo-Flex™ FFC Jumper, Opposite Side Contacts (Type D), 30 Circuits, 0.254m Cable Length, 0.22mm Cable Thickness, Tin(Sn) Plating



image - Reference only

Series

Documents:

Drawing (PDF)

Product Specification PS-98268-001 (PDF)

Packaging Specification PK-98268-001 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Cable

Series

98268

Comments

Contacts on opposite sides, Type D

Crimp Quality Equipment

Yes

Overview

Premo-Flex™ FFC and Etched Polyimide Jumpers

Product Name

Premo-Flex™ FFC Jumper

UPC

756054778920

Physical

Cable Length

0.254m

Circuits (Loaded)

30

Net Weight

6.476/g

Packaging Type

Bag

Pitch - Termination Interface

1.25mm

Temperature Range - Operating

-40°C to +105°C

Wire Size AWG

N/A

Wire/Cable Type

Flat Flex Cable

Electrical

Current - Maximum per Contact

1.4A

Voltage - Maximum

60V AC

Material Info

Reference - Drawing Numbers

Packaging Specification

PK-98268-001

Product Specification

PS-98268-001

Sales Drawing

SD-98268-001

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

98268Series

Use With

Molex FFC – FPC connector.
Be sure to match like plating

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION