



ENCLOSURES 
Right Now, Right Price.



[Home](#) | [Contact Us](#)

Search Our Site



440-946-3200

[ABOUT US](#)

[REPRESENTATIVES](#)

[DISTRIBUTORS](#)

[RESOURCE CENTER](#)

[WHAT'S NEW](#)

[Check Stock
Pricing](#)

Part Number



Large Cabinet Racks

BudRack Professional Series



Design Features

- Sturdy and durable steel construction - Mounting rails - 14 GA, other parts 18 GA.
- Finished complete with ventilated tempered glass front door, locking rear door, removable sides
- EIA 310 Compliant for [19" rack-mount equipment](#)
- Two pairs of fully adjustable panel mounting rails included. The panel mounting rails include unique notch at each "U" point to allow for rapid equipment location identification
- Top mount fan box installed. Two fans for 23" depth, four fans for 31" depth
- Includes ventilated shelves (one shelf in the 24U high cabinet, two shelves in the 40U and 45U cabinets)
- Includes four casters and four levelers (unassembled)
- Large cutout in base. Cutout comes covered by 2.5" deep metal cover plates that allow for adjustable opening providing as much or as little open space for cable access
- Two (2) additional 13" x 2.5" cutouts in front and rear of base also come with readily removable covers
- Vented at top and bottom of sides, which also can be locked
- Comes fully assembled
- Finish: Black textured powder coating - easy to clean.
- Other sizes and modifications are available upon request.

BudRack Professional Series											
Catalog No.	Drawings	Panel Space (inches)		"U"	Overall Dimensions (inches)			Clear Inside Depth (inches)	Weight (Lbs.)	Additional Ventilated Fixed Shelf Catalog No.	Weight (Lbs.)
		Width	Height		Width	Depth	Height				
BRP-12202	PDF DXF	19.00	42.00	24	23.62	23.62	49.40	20.88	222	SH-12706	5
BRP-12206	PDF DXF	19.00	70.00	40	23.62	23.62	77.40	20.88	305		
BRP-12208	PDF DXF	19.00	78.75	45	23.62	23.62	86.15	20.88	327		
BRP-12212	PDF DXF	19.00	42.00	24	23.62	31.50	49.40	28.75	254	SH-12708	6
BRP-12216	PDF DXF	19.00	70.00	40	23.62	31.50	77.40	28.75	345		
BRP-12218	PDF DXF	19.00	78.75	45	23.62	31.50	86.15	28.75	370		