


2.5mm Right Angle 4 Conductor Cable

172-MC254-EX

KOBICONN

2.5mm Right Angle 4 Conductor Cable



Dimensions: mm (in)

SPECIFICATIONS	
Pole:	4
Conductor:	10/0.12X3
Insulator:	O.D. 0.8mm
Shield:	32/0.12
Sheath:	O.D. 3mm
Rated Voltage:	30V
Operating Temperature:	60°C Max.
Mates with	161-2828-E
RoHS Compliant by Exemption	

Date Last Revised: 7-17-07

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC-301157

172-MC254-EX

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[172-MC254-EX](#)