

Harting


Han 3 A 3 + $\frac{1}{2}$	Screw Terminal	Side Entry Hood	Gland	Top Entry Hood	Gland	Panel Mount Housing	Surface Mount Housing	Cable to Cable	Gland	Gland
Working Voltage			250V		20mm				20mm	A20
Working Current										
Wire Gauge										
	(M) 09 20 003 2611	19 20 003 1640		19 20 003 1440	20mm	09 20 003 0301	19 20 003 1250	19 20 003 1750		
	(F) 09 20 003 2711									


Han 6 E 6 + $\frac{1}{2}$	Screw Terminal	Side Entry Hood	Gland	Top Entry Hood	Gland	Panel Mount Housing	Surface Mount Housing	Two Side-Entry	Gland	Gland
Working Voltage			380V		20mm				20mm	A20
Working Current										
Wire Gauge										
	(M) 09 33 006 2601	L 19 30 006 1540		L 19 30 006 1440	20mm	09 30 006 0301	19 30 006 1250	19 30 006 1290	20mm	2x20mm
	(F) 09 33 006 2701	H 19 30 006 1541		H 19 30 006 0446	25mm	with thermoplastic cover 09 30 006 0302	with thermoplastic cover 19 30 006 1255	with thermoplastic cover 19 30 006 1295		A20
		H 19 30 006 0547		H 19 30 006 0447	32mm				20mm	

Han 10 E 10 + $\frac{1}{2}$	Screw Terminal	Side Entry Hood	Gland	Top Entry Hood	Gland	Panel Mount Housing	Surface Mount Housing	Two Side-Entry	Gland	Gland
Working Voltage			380V		20mm				20mm	A20
Working Current										
Wire Gauge										
	(M) 09 33 010 2601	L 19 30 010 1540		L 19 30 010 1440	20mm	09 30 010 0305	19 30 010 1250	19 30 010 1290	20mm	2x20mm
	(F) 09 33 010 2701	H 19 30 010 1541		H 19 30 010 1441	25mm	with thermoplastic cover 09 30 010 0303		with thermoplastic cover 19 30 010 1295		A20
		H 19 30 010 0547		H 19 30 010 0447	32mm					

L = Low Construction H = High Construction

Harting

Han 10 E 16 + $\frac{1}{2}$				Screw Terminal	Side Entry Hood	Gland	Top Entry Hood	Gland	Panel Mount Housing	Surface Mount Housing	Gland	Two Side-Entry	Gland	Gland
Working Voltage	380V				2 levers on the Housing 		2 levers on the Housing 		2 levers on the Housing 	2 levers on the Housing 		2 levers on the Housing 		
Working Current	16A													
Wire Gauge	2,5mm													
					L 19 30 010 1520	20mm	L 19 30 010 1420	20mm	09 30 010 0301	L 19 30 010 1230	20mm	L 19 30 010 1270	2x20mm	A20
					H 19 30 010 1521	25mm	H 19 30 010 1421	25mm		L 19 30 010 1231	25mm	L 19 30 010 0271	2x25mm	A22
					H 19 30 010 0527	32mm	H 19 30 010 0427	32mm		H 19 30 010 0231	25mm	L 19 30 010 0272	2x32mm	A23

Han 16 E 16 + $\frac{1}{2}$				Screw Terminal	Side Entry Hood	Gland	Top Entry Hood	Gland	Panel Mount Housing	Surface Mount Housing	Gland	Two Side-Entry	Gland	Gland
Working Voltage	380V				1 lever on the Housing 		1 lever on the Housing 		1 lever on the Housing 	1 lever on the Housing 		1 lever on the Housing 		
Working Current	16A													
Wire Gauge	2,5mm													
				(M) 09 33 016 2601	L 19 30 016 1541	25mm	L 19 30 016 1441	25mm	09 30 016 0307	19 30 016 1251	25mm	19 30 016 1291	2x25mm	A22
				(F) 09 33 016 2701	H 19 30 016 0547	32mm	H 19 30 016 1442	32mm	with thermoplastic cover 09 30 016 0306	with thermoplastic cover 19 30 016 1256	25mm	with thermoplastic cover 19 30 016 1296	2x25mm	A22
							H 19 30 016 0447	32mm						

L = Low Construction H = High Construction