


REV. | U

UNLESS OTHERWISE NOTED

DIMENSIONS ARE IN INCHES		TOLERANCES ARE:	
ONE PLACE DECIMALS ± .1 [3]	THREE PLACE DECIMALS ± .005 [.13]		
TWO PLACE DECIMALS ± .01 [.3]	FOUR PLACE DECIMALS ± .0020 [.051]		

ANGLES ± 2°	TITLE: LOW PROFILE SOCKET STRIP
----------------	---------------------------------------

DWG NO:
SLW-1XX-01-X-X
SHEET 1 OF 1



SLW-1XX-01-X-X

POSITION SPECIFICATION —
 -01 THRU -50 PER ROW
 "A" = NO. OF POS. x .100 [2.54]

— ROW SPECIFICATION
 —D: DOUBLE (USE SLW-50-D)
 —S: SINGLE (USE SLW-50-S)




CONTACT STYLE
-01: USE C-28-X

PLATING SPECIFICATION

- G: GOLD-SPECIFY -G IN CONTACT SUFFIX -X
- T: TIN-SPECIFY -T IN CONTACT SUFFIX -X
- S: SELECTIVE GOLD, MATTE TIN TAIL-SPECIFY -S IN CONTACT SUFFIX -X
- F: FLASH SELECTIVE GOLD-SPECIFY -F IN CONTACT SUFFIX -X
- H: HEAVY GOLD-SPECIFY -H IN CONTACT SUFFIX -X
- L: LIGHT SELECTIVE GOLD, MATTE TIN TAIL-SPECIFY -L IN CONTACT SUFFIX -X

NOTES:

1. MIN PUSHOUT FORCE: 1 lb.
 2. MAX BOW: .005 in/in [mm/mm], .025 [.64]
 3. CUT END WALLS TO BE .012 [.30] MIN.
 4. (C) REPRESENTS CRITICAL DIM.
- FOR STATISTICAL PROCESS CONTROL.
5. .010 [.25] MAX CUT FLASH
 6. NO TUBE PACKAGING REQUIRED



PLOT SCALE: 1=.1

samtec

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
PHONE (812) 944-6733 P.O. BOX 1147

MADE BY:	PURVIS 9-4-87
CHECKED BY:	McCARTIN

ENG. APPROVA DEM

SLW-1XX-01-X-X
SHEET 1 OF 1

Do not scale
from this print

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC INC. AND SHALL NOT BE
REPRODUCED OR TRANSFERRED TO
OTHER DOCUMENTS OR DISCLOSED TO
OTHERS OR USED FOR ANY PURPOSE
OTHER THAN THAT FOR WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED
WRITTEN CONSENT OF SAMTEC INC.