


MATERIALS:

Body: Brass, H.H. per QQ-B-626, Alloy 360

Insulation: RNF-100 shrink Tubing, Black.

Finish: Body: Electroless nickel plated per MIL-C-26074, Class 2 (.0002 min.) over copper strike.

RATINGS:

Operating Voltage: 300V

Operating Temperature: +102°C (+216°F) Max.

Current: 5 Amperes

ORDERING INFORMATION: Model 4311-*

*= Color, -0 Black, -2 Red

Part is packaged one (1) per bag, unassembled.

Part mates with Pomona Model 4011

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA