




SPECIFICATIONS

Current Rating: 3 Amperes

Insulation Resistance: 1000M Ω Min

Dielectric Withstanding: 600V AC/DC

Contact Resistance: 20m Ω Max.

Operating Temperature: -40°C to +105°C

MATERIALS

Contact Material: Copper Alloy

Contact Plating: Gold / Tin over Nickel

Insulator: Glass Filled Polyester (UL 94V-0)

P.B.T or Nylon-6T

All materials must be RoHS compliant.

Terminal Code	Dimensions(mm)		
	A	B	C
QA	10.20	5.20	2.50
X QB	10.80	5.80	2.50
QC	11.60	5.80	3.30
QD	12.60	6.80	3.30
QE	14.00	8.20	3.30
QF	14.80	9.00	3.30
QG	17.90	12.10	3.30
X QH	19.80	14.00	3.30
QJ	21.60	15.80	3.30
QK	22.80	17.00	3.30
QL	24.90	19.10	3.30
NP	11.60	6.00	3.10
NQ	11.80	6.00	3.30
NR	12.60	7.00	3.10
NS	13.50	8.00	3.00
NT	14.20	8.70	3.00
NU	16.00	10.50	3.00
NV	18.00	12.50	3.00
NW	20.00	14.50	3.00
TM	14.50	8.90	3.10
TN	11.30	5.50	3.30
TZ	11.80	5.70	3.60

Datenblatt passend zu folgenden Artikelnummern

10120514 / 10120516 / 10120518 / 10120520

10120168 / 10120169 / 10120170 / 10120171 / 10120172 / 10120173