



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
G	14		F	REV PER 0G3A-0319-03	27MAY03	JR	TM




- 1. INSULATION DIA .250 MAX
- 2. FITS TAB .032 THK

AMP WIRE RANGE	 FILE E66717	 LR7189 Certified
12-10 AWG STRANDED	12-10 AWG STRANDED	12-10 AWG STRANDED



—	—	640906-1
QTY	PACKAGE TYPE	PART NO

TYCO ELECTRONICS CUSTOMER SERVICE SYSTEM		MAX RECOMMENDED OPERATING TEMPERATURE: 105°C —	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L OLMEDA 26JUN95	 Tyco Electronics Corporation Harrisburg, PA 17105		
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWING AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752				CHK M ELLIS 26JUN95			
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	VOLTAGE RATING: 300V MAX —	DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD B BARE 26JUN95	NAME RECEPTACLE, 250 SERIES, FASTON , PIDG , 12-10		
FOR ORDER ENTRY	1-800-526-5142	CIRCULAR MIL AREA: 5,180-13,100 STRANDED		0 PLC ± — 1 PLC ± — 2 PLC ± .015 3 PLC ± — 4 PLC ± — ANGLES ± —	PRODUCT SPEC UL 310			
			MATERIAL BODY,BRASS .018	FINISH BODY,TIN	APPLICATION SPEC 114-1002	SIZE A3	CAGE CODE 00779	DRAWING NO C-640906
					WEIGHT —	RESTRICTED TO —		
					CUSTOMER DRAWING	SCALE 6:1	SHEET 1 OF 1	REV F