





DIMENSIONS: mm (in.)
(except where noted)

SPECIFICATIONS	
Type:	Chassis mount DC power w/solder lugs
Rating:	100VDC 2A
Insulation resistance:	50M Ω min. @ 100VDC
Contact resistance:	30m Ω max.
Dielectric strength:	250VAC for 1 minute
"L" lug, contact pin, nut, body:	Nickel plated brass
Spring:	Nickel plated phosphor bronze
Insulator:	Delrin
Mounting hole:	$\phi 4.45 \pm 0.028$ "
Pin size:	$\phi 2.0 \pm 0.5$ mm (163-4021), $\phi 2.4 \pm 0.5$ mm (163-4025)
Max panel thickness:	5mm

Date Last Revised: 6/17/09

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300372

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Kobiconn:

[163-4025](#) [163-4021](#)