

MATERIALS AND FINISHES:

BODY BRASS
PLATED SEE TABLE

CONTACT BERYLLIUM COPPER
PLATED GOLD



INSULATOR TEFLON

GASKET SILICONE RUBBER



LOCKWASHER PHOSPHOR BRONZE
PLATED GOLD

JAMNUT BRASS
PLATED GOLD


CRIMP TUBE BRASS
PLATED GOLD





CONTACT




JAMNUT



RECOMMENDED STRIP DIMENSION
CRIMP SIZE: .128 HEX



LOCKWASHER



GASKET

MIL-STD-348A, FIG. 310.2	INTERFACE
SPECIFICATION	DESCRIPTION

73251-2172	73251-2170 PACKAGED IN SINGLE BAGS
73251-2171	GOLD (5 MICROINCHES MIN) / BULK PACK
73251-2170	GOLD (1 MICROINCHES MIN) / BULK PACK
PART NO.	PLATING / PACKAGING

SPECIFICATION		DESCRIPTION		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION	
								MM/IN				METRIC			
CHG: ADD -2172 EC NO: URF2012-0421 DRWN: WIENER CHKD: SSS APPR: WIENER		2012/01/26 2012/01/26 2012/01/27		QUALITY SYMBOLS ▽=0 ▽=0		4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± --- ± --- 1 PLACE ± --- ± --- ANGULAR ± 2 °		DRAWN BY DATE SSS 2004/02/10 CHECKED BY DATE TEF 2004/02/10 APPROVED BY DATE GMH 2004/02/10		TITLE SMA JACK, BLKHD, RG316 50 OHM, EWR2051 SMA-JC/BLK		MATERIAL NO. SEE TABLE		DOCUMENT NO. SD-73251-217	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		REV		A3		SIZE		C		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		SHEET NO. 1 OF 1			