

Pt 100 Probes

	General purpose		Immersion		Insertion		Air probe	
Probe type	SE011	SE019	SE012	SE014	SE015	SE016	SE017	SE018
Temperature range	-30 to +200 °C	-75 to +260 °C	-50 to +250 °C	-75 to +250 °C	-75 to +250 °C	-150 to +650 °C	-75 to +250 °C	-150 to +650 °C
Accuracy	±0.15 °C @ 0 °C	±0.15 °C @ 0 °C	±0.03 °C @ 0 °C	±0.15 °C @ 0 °C	±0.15 °C @ 0 °C	±0.15 °C @ 0 °C	±0.15 °C @ 0 °C	±0.15 °C @ 0 °C
Dimensions: Length (mm) Diameter (mm): Cable (m)	150 6 2	120 3 2	150 4 2	120 3.3 2	120 3.3 2	150 4 2	120 3.3 2	150 4 2
Material	s/s probe PVC cable	s/s probe PVC cable	s/s probe PTFE cable	s/s probe PVC cable	s/s probe PVC cable	s/s probe PVC cable	s/s probe PVC cable	s/s probe PVC cable
Handle	No	Yes	No	Yes	Yes	Yes	Yes	Yes
Order code		1671127		1671123		1671124	1671125	1671126