

CARDMASTER PC 30/25-3



Order symbol: PC 30/25-3
Product nbr: 7525019
Description: Enclosure, PC
Remarks: Smoked transparent hinged cover

EAN: 6418074056740
El. number:
Finland: 3438233
Denmark: 8212016677
Sweden: 2537308
Norway: 2536927

Including: Base, terminal compartment cover with EPDM gasket and screws for mounting plate/DIN-rail. -3 and -L3 versions: Transparent cover with PUR gasket, hinges, locking devices; FC version: Closed PC frame front plate with PUR gasket and cover screws.

Sample photo

Dimensions:		Length	Width	Height	Rating:
mm:		320	260	129	Ingress Protection (EN 60529): IP 65
inch:		12.6	10.2	5.1	Impact Resistance (EN 62262): IK 08/07
Materials:					Electrical insulation: Totally insulated
Material:		Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:		RAL 7035			UV resistance: UL 508
Cover colour:		Smoked grey			Flammability Rating (UL 746 C 5): UL 746C 5V
Gasket material:		EPDM and Polyurethane			Glow Wire Test (IEC 695-2-1) °C: 960
Temperatures:					NEMA Class: NEMA 1, 3, 3R, 12, 13
Short term:		-40 ... 120 °C			Certificates:
Continuous:		-40 ... 80 °C			
Short term:		-40 ... 250 °F			
Continuous:		-40 ... 175 °F			
Accessories:					Underwriters Laboratories
MP 30/25		Mounting plate			Fimko
FP 30/25		Front plate (aluminium)			Europe EN 62208: 2003
FC PC 30/25		Frame of PC front plate			UL Canada
					Gost R

CARDMASTER 314x260x95-129

