


Honeywell




	<25mΩ (initial)
	>100MΩ@500V DC
	Free position:<10G, Maximum position <30G
	10 to 55 Hz, 1.5 mm double amplitude (excluding spring coil type)



- $OF_{\max}$ 7.35N
- $RF_{\min}$ 0.98N
- $PT_{\max}$ 20°
- $OT_{\min}$ 50°
- $MD_{\max}$ 12°

<HLS-B>




动作特性
快动式




- OF_{max} 7.35N
- RF_{min} 0.98N
- PT_{max} 20°
- OT_{min} 50°
- MD_{max} 12°

<HLS-C>




动作特性
快动式




- OF_{max} 7.35N
- RF_{min} 0.98N
- PT_{max} 20°
- OT_{min} 50°
- MD_{max} 12°

<HLS-D>




动作特性
快动式




- OF_{max} 8.83N
- RF_{min} 1.47N
- PT_{max} 1.5mm
- OT_{min} 4mm
- MD_{max} 1mm

<HLS-H>



动作特性
快动式



- OF_{max} 8.83N
- RF_{min} 1.47N
- PT_{max} 1.5mm
- OT_{min} 4mm
- MD_{max} 1mm