



[TAG[MainCharacteristics]]

產品範圍	Harmony XB4
產品或部件的類型	Head for illuminated push-button
產品相容性	Integral LED
設備簡稱	ZB4
Bezel material	Chromium plated metal
Mounting diameter	22 mm
Sale per indivisible quantity	1
Shape of signaling unit head	Round
Type of operator	Push-push
Operator profile	Red projecting unmarked

[TAG[ComplemCharacteristics]]

CAD overall width	29 mm
CAD overall height	29 mm
CAD overall depth	33 mm
產品重量	0.026 kg
Resistance to high pressure washer	7000000 Pa at 55 °C, distance: 0.1 m
Mechanical durability	500000 cycles
Electrical composition code	M10 對於 <= 2 contacts using single blocks in front mounting with integral LED M6 對於 <= 2 contacts using single blocks in front mounting with integral LED and transformer M5 對於 <= 2 contacts using single blocks in front mounting with integral LED

[TAG[EnvCharacteristics]]

Protective treatment	TH
對於存儲的環境空氣溫度	-40...70 °C
對於運行的環境空氣溫度	-25...70 °C
Class of protection against electric shock	Class I 符合 IEC 60536
IP degree of protection	IP66 符合 IEC 60529
NEMA degree of protection	NEMA 13 NEMA 4X
IK degree of protection	IK05 符合 IEC 50102
標準	EN/IEC 60947-1 EN/IEC 60947-5-1 EN/IEC 60947-5-4 EN/IEC 60947-5-5 JIS C 4520 UL 508 CSA C22.2 No 14
產品認證	BV CSA DNV GL LROS (Lloyds register of shipping) RINA UL listed
Vibration resistance	5 gn (f = 2...500 Hz) 符合 IEC 60068-2-6
Shock resistance	30 gn (duration = 18 ms) 對於 half sine wave acceleration 符合 IEC 60068-2-27 50 gn (duration = 11 ms) 對於 half sine wave acceleration 符合 IEC 60068-2-27