




Shielded Power Inductors – DT1608C



- Low temperature rise allows use at up to 150% of rated current.
- “Swinging” inductance allows use as high L inductors.

Core material Ferrite

Ambient temperature –40°C to +85°C

Maximum part temperature +105°C (ambient + temp rise)

Storage temperature Component: –40°C to +105°C.

Tape and reel packaging: –40°C to +80°C

Resistance to soldering heat Three reflows at >217°C for 90 seconds (+260°C ±5°C for 20 – 40 seconds), allowing parts to cool to room temperature between.

Moisture Sensitivity Level (MSL) 1 (unlimited floor life at <30°C / 85% relative humidity)

Failures in Time (FIT) / Mean Time Between Failures (MTBF)

38 per billion hours / 26,315,789 hours, calculated per Telcordia SR-332

PCB washing Tested to MIL-STD-202 Method 215 plus an additional aqueous wash. See [Doc787_PCB_Washing.pdf](#).

Coilcraft will continue to manufacture and support the DT1608C indefinitely. For new designs, consider the LPS4018 as an alternative to this series. The LPS4018 series is more cost effective, features a smaller footprint, lower profile and better current handling.

Specifications				Operating Parameters			
Part number ¹	Inductance ² ±20% (µH)	DCR max (Ohms)	SRF typ (MHz)	Inductance rating ³ (µH)	Current rating ⁴ (A)	Energy storage max (µJoules)	Switching frequency max
DT1608C-102ML	1.0	0.065	180	0.60	2.0	1.8	1 MHz
DT1608C-152ML	1.5	0.070	120	0.80	1.9	1.8	1 MHz
DT1608C-222ML	2.2	0.075	100	0.90	1.5	1.8	1 MHz
DT1608C-332ML	3.3	0.080	70	1.5	1.2	1.4	1 MHz
DT1608C-472ML	4.7	0.085	60	2.0	1.2	1.6	1 MHz
DT1608C-682ML	6.8	0.090	50	3.0	1.0	1.9	1 MHz
DT1608C-103ML	10	0.125	45	5.0	0.7	1.2	1 MHz
DT1608C-153ML	15	0.135	35	6.0	0.6	1.1	1 MHz
DT1608C-223ML	22	0.160	25	10	0.5	1.2	1 MHz
DT1608C-333ML	33	0.275	20	12	0.45	1.5	1 MHz
DT1608C-473ML	47	0.300	17	20	0.34	1.3	1 MHz
DT1608C-683ML	68	0.575	14	30	0.29	1.4	1 MHz
DT1608C-104ML	100	1.10	12	40	0.24	1.5	1 MHz
DT1608C-154ML	150	1.40	7.0	60	0.20	1.4	500 kHz
DT1608C-224ML	220	2.25	7.0	90	0.17	1.6	500 kHz
DT1608C-334ML	330	2.90	6.0	100	0.16	1.4	500 kHz
DT1608C-474ML	470	3.60	4.0	150	0.14	1.5	500 kHz
DT1608C-684ML	680	4.55	3.5	200	0.12	1.4	500 kHz
DT1608C-105ML	1000	8.10	2.5	400	0.08	1.4	500 kHz

1. When ordering, please specify **termination** and **packaging** codes:

DT1608C-106MLC

Termination: **L** = RoHS compliant electroplated gold (<50 µin) over nickel over moly-manganese.
Special order: **T** = RoHS tin-silver-copper (95.5/4/0.5) or **S** = non-RoHS tin-lead (63/37).

Packaging: **C** = 7" machine-ready reel. EIA-481 embossed plastic tape (750 parts per full reel).

B = Less than full reel. In tape, but not machine ready.
To have a leader and trailer added (\$25 charge), use code letter **C** instead.

D = 13" machine-ready reel. EIA-481 embossed plastic tape (2500 parts per full reel).

2. Inductance tested at 0.1 Vrms, 100 kHz, 0 Adc.

3. Measured at the rated current. Refer to L vs Current curves for details.

4. Average maximum allowable current. DT Series inductors are designed for current spikes as high as twice the current rating.

5. Electrical specifications at 25°C.

Refer to Doc 362 "Soldering Surface Mount Components" before soldering.

SPICE models ON OUR WEB SITE

Document 178-1 Revised 05/20/10

© Coilcraft Inc. 2017

This product may not be used in medical or high risk applications without prior Coilcraft approval. Specification subject to change without notice. Please check web site for latest information.





www.coilcraft.com

US +1-847-639-6400 sales@coilcraft.com
UK +44-1236-730595 sales@coilcraft-europe.com
Taiwan +886-2-2264 3646 sales@coilcraft.com.tw
China +86-21-6218 8074 sales@coilcraft.com.cn
Singapore + 65-6484 8412 sales@coilcraft.com.sg




Shielded Power Inductors – DT1608C Series

Typical L vs Current



Current Derating



Weight: 136– 157 mg

Tape and reel: 750/7" reel; 2500/13" reel 12 mm tape wide, 0.28 mm thick, 8 mm pocket spacing, 3.0 mm pocket depth.