



Sample photo

Order symbol: PC 200/100 HT
Product nbr: 6011927

Description: Enclosure, PC
Remarks: Smoked transparent cover

EAN: 6418074022486
El. number:
Finland 3420483
Denmark 8212022535
Italy 7352125
Sweden 2535672

Including: Base with TPE gasket and screws for mounting plate/DIN-rail, cover with polyamide cover screws and wing heads for cover screws.

Dimensions:			
	L	W	H
mm:	255	180	100
inch:	10	7.1	3.9
Materials:			
Material:	PC		
Base colour:	RAL 7035		
Cover colour:	Smoked grey		
Cover screws material:	Polyamide		
Cover screws colour:	Black		
Gasket material:	TPE		
Temperatures:			
Short term:	-40 ... 120 °C		
Continuous:	-40 ... 80 °C		
Short term:	-40 ... 250 °F		
Continuous:	-40 ... 175 °F		
Accessories:			
MIV 200	Mounting plate		
MIN 15	DIN-15 Mounting rail		
MIN 20	DIN-15 Mounting rail		
MIV 15	DIN-35 Mounting rail		
MIV 20	DIN-35 Mounting rail		
FP A 200/180	Front plate		
HFP 180	Front plate hinge series		

Rating:
Ingress Protection (EN 60529): IP 66/67
Impact Resistance (EN 50102): IK 08
Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): Yes
UV resistance: UL 508
Flammability Rating (UL 746 C 5): UL 94 5V
Glow Wire Test (IEC 695-2-1) °C: 960
NEMA Class: NEMA 1, 4, 4X, 6, 12, 13
Certificates:
Germanischer Lloyd (GL)
Underwriters Laboratories
Det Norske Veritas
Fimko
Europe EN 50298 1998
UL Canada
Gost R

