

Wirewound, Surface Mount, Molded, Shielded Inductors



STANDARD ELECTRICAL SPECIFICATIONS

IND. (μ H)	TOL.	TEST FREQ. (MHz)	Q MIN.	SRF MIN. (MHz)	DCR MAX. (Ω)	RATED DC CURRENT (mA) ⁽¹⁾
0.010	$\pm 20\%$	50	50	1000	0.10	810
0.012	$\pm 20\%$	50	50	1000	0.11	750
0.015	$\pm 20\%$	50	50	1000	0.12	720
0.018	$\pm 20\%$	50	50	1000	0.13	690
0.022	$\pm 20\%$	50	45	1000	0.15	640
0.027	$\pm 20\%$	50	45	1000	0.17	610
0.033	$\pm 20\%$	50	45	1000	0.18	585
0.039	$\pm 20\%$	50	40	1000	0.24	530
0.047	$\pm 20\%$	50	40	1000	0.26	495
0.056	$\pm 20\%$	50	40	1000	0.28	485
0.068	$\pm 20\%$	50	40	1000	0.35	475
0.082	$\pm 20\%$	50	38	900	0.45	460
0.10	$\pm 20\%$	50	36	700	0.50	450
0.12	$\pm 20\%$	25.2	40	500	0.20	630
0.15	$\pm 20\%$	25.2	40	470	0.20	600
0.18	$\pm 20\%$	25.2	40	400	0.24	580
0.22	$\pm 20\%$	25.2	40	330	0.30	565
0.27	$\pm 20\%$	25.2	40	310	0.33	500
0.33	$\pm 20\%$	25.2	40	280	0.36	475
0.39	$\pm 20\%$	25.2	40	230	0.40	465
0.47	$\pm 20\%$	25.2	40	220	0.44	460
0.56	$\pm 20\%$	25.2	40	200	0.46	455
0.68	$\pm 20\%$	25.2	40	180	0.48	450
0.82	$\pm 20\%$	25.2	40	160	0.50	450
1.0	$\pm 10\%$	7.96	30	120	0.60	400
1.2	$\pm 10\%$	7.96	30	110	0.65	390
1.5	$\pm 10\%$	7.96	30	90.0	0.75	370
1.8	$\pm 10\%$	7.96	30	85.0	0.85	350
2.2	$\pm 10\%$	7.96	30	65.0	0.90	320
2.7	$\pm 10\%$	7.96	30	60.0	1.00	290
3.3	$\pm 10\%$	7.96	30	60.0	1.10	270
3.9	$\pm 10\%$	7.96	30	58.0	1.20	250
4.7	$\pm 10\%$	7.96	30	52.0	1.25	220
5.6	$\pm 10\%$	7.96	30	50.0	1.40	210
6.8	$\pm 10\%$	7.96	30	40.0	1.60	205
8.2	$\pm 10\%$	7.96	30	35.0	1.65	195
10.0	$\pm 10\%$	2.52	30	30.0	2.00	185
12.0	$\pm 10\%$	2.52	30	24.0	2.30	175
15.0	$\pm 10\%$	2.52	30	20.0	2.50	165
18.0	$\pm 10\%$	2.52	30	17.0	2.70	155
22.0	$\pm 10\%$	2.52	30	16.0	3.10	150
27.0	$\pm 10\%$	2.52	30	14.5	3.30	125
33.0	$\pm 10\%$	2.52	30	14.5	5.10	115
39.0	$\pm 10\%$	2.52	30	14.0	5.90	105
47.0	$\pm 10\%$	2.52	30	13.0	8.00	100
56.0	$\pm 10\%$	2.52	30	11.5	10.0	95
68.0	$\pm 10\%$	2.52	30	11.0	10.0	90
82.0	$\pm 10\%$	2.52	30	11.0	11.0	85
100.0	$\pm 10\%$	0.796	30	6.0	12.0	80

Note

(1) Rated DC current based on the maximum temperature rise, not to exceed 40 °C at +85 °C ambient

FEATURES

- Molded construction provides superior strength and moisture resistance
- Tape and reel packaging for automatic handling, 2000/reel, EIA-481
- Compatible with vapor phase, infrared and wave soldering methods
- Shielded construction minimizes coupling to other components
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT
HALOGEN
FREE

ELECTRICAL SPECIFICATIONS

Inductance range: 0.01 μ H to 100 μ H

Special tolerances available upon request


Operating temperature: -55 °C to +125 °C

Coilform material: Non-magnetic for 0.01 μ H to 0.10 μ H; powdered iron for 0.12 μ H to 100 μ H

TEST EQUIPMENT

- H/P 4342A Q meter with Vishay Dale test fixture or equivalent
- H/P 4191A RF impedance analyzer (for SRF measurements)
- Wheatstone bridge

DIMENSIONS in inches [millimeters]



Note

(1) Recommended minimum spacing between components

PART MARKING

- Vishay Dale
- Inductance value
- Date code

DESCRIPTION

ISC-1210	10 μ H	$\pm 10\%$	ER	e3
MODEL	INDUCTANCE VALUE	INDUCTANCE TOLERANCE	PACKAGE CODE	JEDEC® LEAD (Pb)-FREE STANDARD

GLOBAL PART NUMBER

I	S	C	1	2	1	0	E	R	1	0	0	K
PRODUCT FAMILY			SIZE				PACKAGE CODE		INDUCTANCE VALUE			TOL.



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.