

GP Batteries

Data Sheet


Model No.: GP13G

NO MERCURY ADDED

Description	: Mercury Free Extra Heavy Duty Battery, D Size
Chemical System	: Zinc Chloride
Nominal Voltage	: 1.5 Volts
Nominal Dimensions	: Ø34.2 mm x 61.5 mm
Terminals	: Protruded positive(+) and flat negative(-) contacts
Jacket	: Metal jacket with PVC tube insulation
Applications	: All electronic devices, e.g. transistor radios, cassette recorders, toys, alarm clocks, portables fans, portables hand-tools.
Shelf Life	: 24 months
Average Weight	: 102g
Date Code	: Unless otherwise specified, every battery will carry an expiry date code for 24 months. (e.g. a battery manufactured on January 2000 will carry an expiry code of 01-02.) 01 stands for January, 02 stands for 2002

Typical Service Life:

Discharge Resistance	Discharge Condition	End Point Voltage	Service Life
39 Ohms	4 Hrs/ Day	0.9V	200 Hrs
3.9 Ohms	1 Hr/ Day	1.0V	12.1 Hrs



Cross References:

GP	JIS	IEC	Eveready
13G	R20P	R20	1250

