








Specifications:

Current rating:3.0A AC,DC

Voltage rating:250V AC,DC

Temperature range:-40°C ~ +85°C

Contact resistance:30mohm max.

Insulation resistance: 5,000Mohm min.

Withstanding voltage:1,000V AC/Minute

Materials:

Insulator:High temp.plastic (UL94V-0)

Contact:Copper alloy Nickel Undercoated,
Selective Gold plated

Finish:Metal Iron with Tin plated

How To Order

5501-XXPA-XX-XX-XXF1

Lead Free

Blank:White(Standard Color)

BK:Black; BU:Blue

Blank:Standard type

CS:Rear Rivet

CC:Front Rivet

01:Full Gold Plated

02:Selective Gold

PA:Stamp Pin Male

No.Of Positions

Pos	A	B	C	D	E
9	16.92	24.99	30.81	8.38	12.50
15	25.25	33.32	39.14	8.38	12.50
25	38.96	47.04	53.04	8.38	12.50
37	55.42	63.50	69.32	8.38	12.50
50	52.81	61.11	66.93	11.07	15.37

RoHS Compliant

F			
E			
D			
C			
B			
A	19-Aug-2005	(PC0052)	Cel King
REV	DATE	FILE	BY

DRAWN:
Cel King

CHECKED:
JEREMY LIU

APPROVAL:
MIKE WU

GENERAL TOLERANCE:

.X=±0.2

.XX=±0.15

UNIT: MM

SCALE: 1:1

SHEET: 1 / 1

PROJECTION:



繼德工業股份有限公司
Neltron Industrial Co., Ltd.

DESCRIPTION:

D-SUB Solder Male Stamp Pin Type

PART NO:

5501-XXPA-XX-XX-XXF1

SIZE

A4