





THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTIONS IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
A	INITIAL RELEASE	03/22/06	D. PARHAM
B	ECN#2347: CONDUCTOR MAX OD WAS .039"	03/24/06	D. PARAHM
C	ECN 2587: REDIMENSION AND REFORMAT	10/30/2006	J. KIEZULAS
D	ECN3213: ADDED PACKAGING SPECIFICATION NOTE	03/03/08	D. PARHAM



NOTES:

MATERIAL:
HOUSING, LOAD BAR, PAIR SEPARATOR: POLYCARBONATE, CLEAR, UL94V-0
CONTACTS: PHOSPHOR BRONZE
SHIELD/STRAIN RELIEF: BRASS

FINISH:

CONTACTS: 50 MICROINCHES [1.27 MICRON] MIN. GOLD IN CONTACT AREA
OVER 100 MICROINCHES [2.54 MICRON] MIN. NICKEL PLATE OVERALL.
CONTACT MATING SURFACE TO BE ELECTROPOLISHED
SHIELD/STRAIN RELIEF: 100 MICROINCHES [2.54 MICRON] NICKEL

ELECTRICAL:

VOLTAGE: 125 VAC. MAX.
CURRENT: 1.5 AMPS MAX.


MECHANICAL:

CONTACT STYLE: 2 PRONG
COMPATIBLE WITH STRANDED AND SOLID CONDUCTORS
CONDUCTOR RANGE: 24 - 26 AWG
MAX. CONDUCTOR INSULATION DIAMETER: .042 [1.07]
PARTS SHALL CONFORM TO TIA-1096

MISCELLANEOUS:

OPERATING TEMPERATURE RANGE: -40°C TO +125°C
TERMINATED CONTACT HEIGHT: .237±.005 [6.02±.13]
FOR TERMINATION OR TOOLING INFORMATION PLEASE VISIT
THE APPROPRIATE PRODUCT PAGE AT WWW.L-COM.COM
PARTS SHALL BE ROHS COMPLIANT

PACKAGE PER PS-0027.



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS		DATE		 NORTH ANDOVER, MA 01845	
OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] - 60 [1524] = +2 [51] / -0 >60 [1524] - 120 [3048] = +4 [102] / -0 >120 [3048] - 300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% DIMENSIONAL TOLERANCE: .X = .3 .XX = .15		DRAWN BY D. PARHAM		03/09/2006		CATEGORY	
		CHECKED BY J. KIEZULAS		03/22/2006		MODULAR	
		APPROVED BY C. McCORMICK		03/22/2006		PRODUCT DESCRIPTION	
		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY				(8X8) CAT 6 SHIELDED PLUG FOR ROUND CABLE	
PROJECTION 		COLOR VARIATIONS MAY OCCUR 1AD03-013		SIZE B	FSCM NO. 43321	DWG. NO. TDS8PC6	REV. D
				SCALE: 4:1		CAD FILE: TDS8PC6.SLDDRW	
						SHEET 1 OF 1	