




Telecommunication ADSL Transformer Components

DT32-2033BS

- Designed to reflect 100Ω on the line with 100Ω on the Ic side.
- For use with Globespan G7000 ADSL Clipset.
- Excellent THD performance.
- Designed to meet UL1950 requirements.



DIMENSIONS IN mm

A	B	C	D	E	F
12.5 MAX	13.8 ± 0.2	17.10 ± 0.2	2.54 ± 0.2	14.6 ± 0.25	

ELECTRICAL CHARACTERISTICS	
TURNS RATIO	N1:N2:N3:N4 1:1:1:1 $\pm 2\%$ @10KHz 0.1V
INDUCTANCE	PRI: 430uH $\pm 10\%$ @10KHz 0.1V
LEAKAGE INDUCTANCE	PRI: 10uH MAX @100KHz 0.1V
D.C RESISTANCE	N1: 0.45 Ω MAX N2: 0.45 Ω MAX N3: 0.35 Ω MAX N4: 0.35 Ω MAX
INSERTION LOSS	0.5dB MAX @722KHz
LONGITUDINAL BALANCE	40dB Min @25KHz~1MHz
TOTAL HARMONIC DISTORTION	-80dB MAX @100KHz, 4.5Vpp
DIELECTRIC STRENGTH	1875 VAC 1 SEC @PRI TO SEC

DELTA ELECTRONICS, INC.

(TAOYUAN PLANT CPBG) 31-1, SHIEN PAN ROAD, KUEI SAN INDUSTRIAL ZONE, TAOYUAN SHIEN, TAIWAN, R.O.C.

TEL: 886-3-3626301; FAX: 886-3-3618901

<http://www.deltaww.com>