



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




ACTUAL SIZE



0.25±0.03 (6.35±0.76)
NOMINAL CABLE O.D.

NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE, AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL.

*PANDUIT PART NO.	WEIGHT LBS / 100 PCS. (g)
AMC25-AT	0.40 (182)



ADHESIVE TAPE: PRESSURE SENSITIVE FOAM .040 (1.02) THICK WITH ACRYLIC ADHESIVE AND PROTECTIVE LINER. MOUNT IS DESIGNED TO SUPPORT .40 lbs. (182g) MAXIMUM WEIGHT ON AA CLEAN, DRY, SMOOTH, GREASE-FREE SURFACE.

- TO APPLY CLIP:
1. REMOVE PROTECTIVE LINER.
 2. PLACE IN DESIRED LOCATION.
 3. APPLY PRESSURE TO CLIP.

NOTES:
*1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.

DIMENSIONS IN BRACKETS ARE METRIC [mm]

CAD FILENAME/LAYERS

G00239FW_DC_AMC25_03

PANDUIT

CORP.

TINLEY PARK, ILLINOIS

AMC25-AT
ADHESIVE MOUNTING CLIP

3	2/10/05	JAD		.788 (20.02) was .84 (21.3)	GB0239FW	3				
2	4/26/04	JAD		CUT LENGTH TOL WAS .02"	GB0239FW	2				
1	8/18/01	LGG		DELETED DIM'S, ADDED REF TO DIM UPDATED FOR WEB	GB0239FW	1				
R	8-20-98	C8SM		INITIAL RELEASE	GB0239FW	R				
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP		

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ±0.05 (1.3) (.XXX) ±0.010 (0.25)
(.XX) ±0.02 (0.5) ANGLES ± 5°

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY

C8SM

MAT'L:

WHITE
PVC

SCALE

NONE

DATE

8-20-98

DRAWING NO.

GB0239FW

DWG

A
SIZE