

SmartPro 2.2kVA Line Interactive UPS, SNMPWEBCARD option, Tower, USB, Serial, 120V

MODEL NUMBER: **SMART2200VS**



Highlights

- 2.2kVA / 2200VA line interactive tower UPS system
- 120V nominal output during brownouts to 79V and overvoltages to 147V
- Front panel status LEDs with load and battery capacity level display
- USB, RS232, EPO and optional SNMP/Web card are available for simultaneous use
- NEMA 5-20P input; 2 NEMA 5-15/20R & 7 5-15R outlets

Package Includes

- SMART 2200VS UPS System, PowerAlert Software and cabling, Instruction manual

Description

Tripp Lite's SMART 2200VS intelligent, line interactive UPS protects server, networking and telecommunications equipment from blackouts, voltage fluctuations and transient surges. Small footprint, tower UPS system occupies only 106 square inches of floor space with a height of only 14.25 inches. Large capacity 2200 VA/ 1600 watt rated UPS system offers 7 minutes runtime at full load and 19 minutes at half load during power failures. Line interactive voltage regulation corrects brownouts as low as 79V and overvoltages as high as 147V to fully regulated 120V nominal output for smooth continuous operation of connected equipment. Includes a total of 9 outlets, 3 pairs of which can be individually powered off and back on via software interface to selectively reboot remote equipment or shed less critical loads to extend battery runtime for more critical loads. Includes slot for internal SNMPWEBCARD, plus 2 DB9 and 2 USB enhanced monitoring ports for unattended shutdown, remote control and monitoring of UPS system and power data. Ships in attractive gray color scheme. Compatible with Tripp Lite's PowerAlert and Watchdog service software.

Features

- 2200VA/1600 watt output capacity accommodates a variety of server, networking and telecom devices
- High power density 2.2kVA UPS system occupies only 106 square inches of floor space with a height of only 14.25 inches
- Compatible with North American 120V/60 Hz power as found in the USA, Canada and Mexico
- Offers 7 minutes runtime with a full load of 2200VA and 19 minutes with a half load of 1100VA
- Line interactive voltage regulation corrects severe brownouts and overvoltages from 79 to 147v back to normal 120v levels without using battery power
- 9 total outlets (7 NEMA5-15R; 2 NEMA5-15/20R)
- Includes NEMA 5-20 straight blade 20 amp input plug connection
- Notification of system status via 5 LEDs and multi-function audible alarms
- Included PowerAlert Software provides e-mail notification of power problems and the simultaneous automatic unattended shutdown of multiple servers
- 4 built-in communications ports (2-DB9, 2-USB) for remote monitoring and unattended shutdown
- Slot for SNMP/web card (part#: SNMPWEBCARD) and environmental sensor (part#: ENVIROSENSE) for remote communications in large IP environments
- Supports Tripp Lite's WatchDog software application to restore unresponsive programs by automatically restarting them and rebooting completely locked computers by automatically switching UPS power off and back on again
- Communication ports support on battery, low battery, power restored, AC line voltage, DC battery voltage, load percentage, battery charge current,



battery capacity, internal UPS temperature and line frequency status messaging. Interface supports timed inverter shutoff after unattended shutdown, activate self-test and 10 second reboot of connected equipment

- 3 pairs of customized load management receptacles can be individually powered off and back on again via software interface to reboot remote equipment or shed less critical loads to extend battery runtime for the most critical equipment
- Built-in Emergency Power Off (EPO) interface supports emergency shutoff in large facilities
- Hot-swappable/user replaceable batteries allow on-site battery replacement without powering off connected equipment
- UPS battery set ships fully assembled and ready for use, no time consuming, connection of individual internal batteries by user is necessary
- UL (USA), cUL (Canada), NOM (Mexico), Class A (Emissions)

Specifications

OUTPUT	
Output Volt Amp Capacity (VA)	2200
Output kVA capacity (kVA)	2.2
Output Watt Capacity (watts)	1600
Output kW capacity	1.6
Output power factor	0.7
Nominal Output Voltage(s) Supported	120V
Frequency compatibility	60 Hz
Output voltage regulation (line mode)	-18% / +8%
Output voltage regulation (Battery mode)	+/- 5%
Built-in UPS output receptacles	7 5-15R outlet(s); 2 5-15/20R outlet(s)
Built-in controllable switched load banks	Three switchable two-outlet 5-15R load banks
Output AC waveform (AC mode)	Sine wave
Output AC waveform (battery mode)	PWM sine wave
INPUT	
Rated input current (at maximum load)	16A
Nominal Input Voltage(s) Supported	120V AC
UPS input connection type	5-20P
Input circuit breaker	20A
UPS Input cord length (ft.)	8
UPS Input cord length (m)	2.4
Recommended Electrical Service	20A 120V
Phase	Single-Phase



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

BATTERY	
Full load runtime (minutes)	7 min. (1600w)
Half load runtime (minutes)	19 min. (800w)
DC system voltage (VDC)	48
Battery recharge rate (included batteries)	Less than 4 hours from 10% to 90%
Replacement battery cartridge (internal UPS battery replacement)	RBC54
Battery Access	Battery access door
Battery replacement description	Hot-swappable, user replaceable batteries
VOLTAGE REGULATION	
Voltage regulation description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 79V to 147V
Overvoltage correction	Input voltages between 128 and 147 are reduced by 12%
Undervoltage correction	Input voltages between 95 and 104 are boosted by 12%
Severe undervoltage correction	Input voltages between 79 and 94 are boosted by 24%
LEDS ALARMS & SWITCHES	
LED Indicators	5 LEDs indicate line power, battery power, overload, voltage regulation and battery low/replace status
Alarms	Audible alarm indicates power-failure, overload and low-battery conditions
Alarm cancel operation	Power-fail alarm can be silenced using alarm-cancel switch; once silenced, alarm will re-sound to indicate low-battery status
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation
SURGE / NOISE SUPPRESSION	
UPS AC suppression joule rating	480
UPS AC suppression response time	Instantaneous
EMI / RFI AC noise suppression	Yes
PHYSICAL	
Installation form factors supported with included accessories	Tower
Primary form factor	Tower
UPS / Power Module dimensions in primary form factor (height x width x depth / inches)	14.2 x 9.2 x 12
UPS / Power Module dimensions in primary form factor (height x width x depth / cm)	36.2 x 23.5 x 30.5



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

UPS / Power Module weight (lbs)	52.4
UPS / Power Module weight (kg)	23.8
UPS Shipping dimensions (height x width x depth / inches)	16 x 14.8 x 19.8
UPS Shipping dimensions (height x width x depth / cm)	40.6 x 37.5 x 50.2
Shipping weight (lbs)	58.8
Shipping weight (kg)	26.7
Cooling method	Fan
UPS housing material	Polycarbonate
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC mode BTU / hr. (full load)	347.2
Battery mode BTU / hr. (full load)	812.9
AC mode efficiency rating (100% load)	94%
Audible Noise	Audible Noise < 47dBA At Front Side 1 Meter
COMMUNICATIONS	
Communications interface	USB; DB9 Serial; Contact closure
Network monitoring port description	Supports detailed monitoring of UPS and site power conditions; 2 USB ports, 1 DB9 serial and 1 DB9 contact closure port (4 total)
PowerAlert software	Included
Communications cable	2 USB and 2 DB9 cables included
WatchDog compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
LINE / BATTERY TRANSFER	
Transfer time	2-4 milliseconds
Low voltage transfer to battery power (setpoint)	79
High voltage transfer to battery power (setpoint)	147
SPECIAL FEATURES	
Cold Start (startup in battery mode during a power failure)	Cold-start operation supported
High availability UPS features	Hot swappable batteries



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Green & high efficiency features	Individually controllable load banks
CERTIFICATIONS	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category A (EMI)
WARRANTY	
Product Warranty Period (Worldwide)	2-year warranty, 3 year with registration. Note: Registration is required for 3-year warranty.
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 Ultimate Lifetime Insurance

Related Items

Optional Products

Model Number	Description	Qty.
DCATV	Network Surge Suppressor - Essential protection for TV/VCR coaxial lines	1
DNET1	Network Surge Suppressor - Essential protection for data and communication lines	1
DTEL2	Network Surge Suppressor - Essential protection for data and communication lines	1
ENVIROSENSE	Monitors temperature, humidity and contact-closure inputs. (Requires SNMPWEBCARD or switched PDU.)	1
PDU1220	Basic PDU / Power Distribution Unit - Safe, reliable power distribution for critical networking equipment	1
PS7224-20	Tripp Lite Power Strip - Multiple outlets wherever you need them	1
SNMPWEBCARD	For remote monitoring and control via SNMP, Web, or Telnet.	1
U022-010	10-ft. USB2.0 A/B Gold Device Cable (A Male to B Male)	1
WATCHDOGSW	WatchDog Service Monitoring / Reboot Software	1
WEXT5-2200-3000	5-Year Extended Warranty - For Smart Line-Interactive and Online Tower or Rack models, 2200-3000VA or less	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at:

<http://www.tripplite.com/sku/SMART2200VS>.

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[SMART2200VS](#)