



LOC	DIST	P	F	REVISIONS			DATE	APPD
				ZONE	LTR	DESCRIPTION		
G	86				P	REV PER 0G3A-0561-01	090CT02	JR/MS



- 1 CIRCULAR MIL RANGE: 550-650 MCM
- 2 TIN PL 0.00381 [0.000150] MIN THK PER ASTM B-545
- 3 CLEANED, UNPLATED



		3	REQ'D	327290-2			
		2	NONE	327290-1			
		2	REQ'D	327290			
		FINISH	SIGHT HOLE	PART NO			
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± 0.51[.020] 3 PLC DEC ± - ANGLES ± - MATERIAL ANNEALED COPPER ASTM B-75		AMP AMP INCORPORATED Harrisburg, Pa. 17105					
DR 02/28/90 DK SCHRUM		NAME TERMINAL, AMPOWER, WIRE SIZE: 600 MCM					
CHK 25JAN95 MS FEHER							
APPD 25JAN95 WJ VOCKROTH							
APPD 25JAN95 TL SHUTTER							
PRODUCT SPEC 108-30200							
FINISH		SIZE	CAGE CODE	DRAWING NO			
SEE TABLE		C	00779	327290			
WEIGHT .574 LB		SCALE 1:1	SHEET 1 OF 1				