

Clamps
Pro-Clamps



01-0703



01-0716

A new design to meet modern clamping requirements. Available in three ranges with throat depths of 80/110 and 140mm. New handles need 30% less effort to apply the same load and built in passive lock eliminates unwanted jaw movement as well as giving easy positioning around the work piece. New I beam section bars give added strength in use. Pro clamp 'L' have T-bar handles.

490396

Description	Throat Depth(in)	Capacity (mm) (in)	Order Code	Price Each
Short	3	200 8	138-9050	
Short	3	300 12	138-9052	
Short	3	400 16	138-9053	
Short	3	600 24	138-9054	
Short	3	800 32	138-9055	
Medium	4.5	300 12	138-9056	
Medium	4.5	400 16	138-9057	
Medium	4.5	600 24	138-9058	
Medium	4.5	800 32	138-9059	
Medium	4.5	1000 40	138-9060	
Large	5.5	400 16	138-9061	
Large	5.5	600 24	138-9062	
Large	5.5	800 32	138-9064	
Large	5.5	1000 40	138-9065	
Large	5.5	1250 50	138-9066	
Large	5.5	1500 60	138-9067	