

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0743021002

Status:

Obsolete

Description:

1.27mm (.050") Pitch SCSI+ Receptacle, Shielded, Low Cost Version, Right Angle, without Latches, 68 Circuits, Screw Hole, 2-56 Thread, 1.980mm (0.078") End Holes, 1.6mm (.062") PCB Thickness

Replacement Part Number:

79059

Documents:

[Drawing \(PDF\)](#)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	I/O Connectors
Series	74302
Application	Board-to-Board
Comments	1.980mm (.078") End Holes
Component Type	Receptacle
Product Name	SCSI+
Replacement Part Number	79059
Type	N/A

Physical

Circuits (Loaded)	68
Circuits (maximum)	68
Durability (mating cycles max)	500
Flammability	94V-0
Lock to Mating Part	Yes
Material - Plating Mating	Gold
Material - Plating Termination	Tin-Lead
Orientation	Right Angle
PC Tail Length	3.18mm (.125"), 4.19mm (.165")
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm (.063")
Packaging Type	Tube
Panel Mount	Yes
Pitch - Mating Interface	1.27mm (.050")
Plating min - Mating	0.381µm (15µ")
Plating min - Termination	1.905µm (75µ")
Polarized to Mating Part	Yes
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-55°C to +75°C
Termination Interface: Style	Through Hole
Wire Size AWG	N/A

Electrical

Current - Maximum per Contact	1A
Shielded	Yes
Voltage - Maximum	30V

Material Info

Reference - Drawing Numbers

Product Specification	PS-74184-001
-----------------------	--------------

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

74302Series

Mates With

70498 plug

This document was generated on 05/09/2011

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION