

1503A Paired - Single-Pair Cable

 	For more information please call 1-800-Belden1 <u>See Put-ups and Colors</u>
--	---

Description:

22 AWG stranded (7x30) TC conductors, PVC insulation, twisted pair, overall Beldfoil shield (100% coverage), 24 AWG stranded TC drain wire, PVC jacket.

PHYSICAL CHARACTERISTICS:

CONDUCTOR:

Number of Pairs	1
Total Number of Conductors	2
AWG	22
Stranding	7x30
Conductor Material	TC - Tinned Copper

INSULATION:

Insulation Material	PVC - Polyvinyl Chloride
Nom. Insulation Wall Thickness	.010 in.
Lay Length	1.75 in.
Twists/ft.	6.86

Pair Color Code Chart :

Number	Color
1	Black & Red

OUTER SHIELD:

Outer Shield Material Trade Name	Beldfoil®
Outer Shield Type	Tape
Outer Shield Material	Aluminum Foil-Polyester Tape
Outer Shield %Coverage	100 %

OUTER SHIELD DRAIN WIRE :

Outer Shield Drain Wire AWG	24
Outer Shield Drain Wire Stranding	7x32
Outer Shield Drain Wire Conductor Material	TC - Tinned Copper

OUTER JACKET:

Outer Jacket Material	PVC - Polyvinyl Chloride
Outer Jacket Nominal Wall Thickness	.020 in.

OVERALL NOMINAL DIAMETER:

1503A Paired - Single-Pair Cable

Overall Nominal Diameter	.142 in.
--------------------------	----------

MECHANICAL CHARACTERISTICS:

Operating Temperature Range	-30°C To +90°C
UL Temperature Rating	60°C
Bulk Cable Weight	14.3 lbs/1000 ft.
Max. Recommended Pulling Tension	25 lbs.
Min. Bend Radius (Install)	1.5 in.

APPLICABLE SPECIFICATIONS AND AGENCY COMPLIANCE:

APPLICABLE STANDARDS:

NEC/(UL) Specification	CM
CEC/C(UL) Specification	CM
EU CE Mark (Y/N)	Yes
EU RoHS Compliant (Y/N)	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005

FLAME TEST:

UL Flame Test	UL1666 Riser
---------------	--------------

PLENUM/NON-PLENUM:

Plenum (Y/N)	N
--------------	---

ELECTRICAL CHARACTERISTICS:

Nom. Characteristic Impedance	38 Ohms
Nom. Inductance	.18 µH/ft
Nom. Capacitance Conductor to Conductor @ 1 KHz	53 pF/ft
Nom. Cap. Cond. to Other Cond. & Shield @ 1 KHz	97 pF/ft
Nominal Velocity of Propagation	66 %
Nominal Delay	1.5 ns/ft
Nom. Conductor DC Resistance @ 20 Deg. C	14.7 Ohms/1000 ft
Nominal Outer Shield DC Resistance @ 20 Deg. C	18 Ohms/1000 ft
Max. Operating Voltage - UL	300 V RMS
Max. Recommended Current	2.9 Amps per conductor @ 25°C

PUT-UPS AND COLORS:

Item	Description	Put-Up (ft.)	Ship Weight (lbs.)	Jacket Color	Notes
1503A 001U1000	2 #22 PVC FS FRPVC	U1000	16	BROWN	
1503A 002U1000	2 #22 PVC FS FRPVC	U1000	16	RED	
1503A 003U1000	2 #22 PVC FS FRPVC	U1000	16	ORANGE	

1503A Paired - Single-Pair Cable

1503A 004U1000	2 #22 PVC FS FRPVC	U1000	16	YELLOW	
1503A 006U1000	2 #22 PVC FS FRPVC	U1000	16	BLUE, LIGHT	
1503A 007U1000	2 #22 PVC FS FRPVC	U1000	16	VIOLET	
1503A 008U1000	2 #22 PVC FS FRPVC	U1000	16	GRAY	
1503A 009U1000	2 #22 PVC FS FRPVC	U1000	16	WHITE	
1503A 010U1000	2 #22 PVC FS FRPVC	U1000	16	BLACK	
1503A N3UU1000	2 #22 PVC FS FRPVC	U1000	16	GREEN, MIL	

Revision Number: 1 Revision Date: 07-27-2005

© Copyright 2006 Belden, Inc
All Rights Reserved.

Although Belden ("Belden") makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with the following environmental regulations: California Proposition 65 Consent Judgment For Wire & Cable Mfgs. (San Francisco Superior Court Nos. 312962 And 320342); EU RoHS (Directive 2002/95/EC, 27-Jan-2003); Material manufactured prior to the compliance date may still be in stock at Belden facilities and in our Distributor's inventory. EU ELV (Directive 2000/53/EC, 18-Sept-2000); EU WEEE (Directive 2002/96/EC, 27-Jan-2003); And EU BFR (Directive 2003/11/EC, 6-Feb-2003). The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information and belief at the date of its publication. The information provided in the Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.