

B2025 -- Liquidtight System



Product Specifications

Product Type	Liquidtight System
Liquidtight System Type	Flexible Nonmetallic Liquidtight Tubing
Trade Size	1/4"
Color	 Black
Material	Co-extruded rigid and flexible PVC.
Operating Temperature	0°F to +140°F (-18°C to +60°C)
Flammability	New York State Office of Fire Prevention and Control. Construction Specification Institute Number 16111.
Conduit ID/OD	.36"/.57" (9.3/14.5)
Bend Radius	1.50" (38.1)
Certifications	UL Recognized, CSA Certified
Voltage Rating	300V Maximum
UPC Number	78358533315
Weight in LBs	0.07
Link to Drawing Library	Click here for Library
Link to PDF Catalog	Click here for Catalog

