


100P160 Series

Receptacle Protection Cap



Interconnect Solutions Worldwide



EXAMPLE PART NUMBER: 100P160-17-1-C-WR4-17	
100P160 =	POLAMCO SERIES
F =	INSERT F FOR FLUOROSILICONE GASKET (STANDARD GASKET MATERIAL: SILICONE)
17 =	SHELL SIZE (TABLE 1)
1 =	MATERIAL (ALUMINIUM ALLOY) CLICK TO SEE OPTIONS
C =	PLATING: CLICK TO SEE OPTIONS
WR =	LANYARD TYPE (TABLE 4)
4 =	LANYARD LENGTH (IN INCHES)
17 =	ATTACHMENT REF. (SEE NOTE 1)

Tel: +44 (0)845 017 1545

DRAWING NOT TO SCALE
DIMENSIONS IN MM

100P160 Series

Receptacle Protection Cap



Interconnect Solutions Worldwide

TABLE 1

SHELL SIZE	A MAX	B THREAD
09	21,0	0.625-0.1P-0.3L-TS
11	24,5	0.750-0.1P-0.3L-TS
13	28,0	0.875-0.1P-0.3L-TS
15	30,0	1.000-0.1P-0.3L-TS
17	34,0	1.1875-0.1P-0.3L-TS
19	37,0	1.250-0.1P-0.3L-TS
21	40,0	1.375-0.1P-0.3L-TS
23	43,0	1.500-0.1P-0.3L-TS
25	47,0	1.625-0.1P-0.3L-TS

TABLE 2

EYELET REF.	F
01	3,2
02	3,7
03	4,3
04	5,3
05	6,4

TABLE 3

RING REF.	E MAX
09	18,0
11	21,4
13	25,8
15	28,8
17	32,0
19	35,0
21	38,3
23	41,7
25	44,6

TABLE 4

CODE	LANYARD TYPE
WR	NYLON COVERED (CLEAR) STAINLESS STEEL WIRE ROPE
TC	TEFLON COVERED (CLEAR) STAINLESS STEEL WIRE ROPE
WG	TEFLON COVERED (OLIVE DRAB) STAINLESS STEEL WIRE ROPE
WB	TEFLON COVERED (BLACK) STAINLESS STEEL WIRE ROPE
WRB	PVC COVERED (BLACK) STAINLESS STEEL WIRE ROPE
LC	LINK CHAIN
BK	BLACK CORD
VGB	1,5mm BLACK POLYESTER CORD EQV. TO DIN83330-E1,5
B	BEAD CHAIN
R	OLIVE DRAB POLYESTER CORD
NB	OLIVE DRAB NYLON CORD
NK	BLACK NYLON CORD

www.polamco.com