

PWS-1409

PWS-1419

9-slot 14.1" TFT LCD Portable Workstation

9-slot 14.1" TFT LCD Ruggedized Portable Workstation



Features

- 9-slot ISA/PCI backplane platform
- Full size mechanical key-switch keyboard with touch-pad
- Built-in amplified stereo speakers
- 14.1" TFT LCD w/1024 x 768 resolution
- Add-on Card Retention bar
- Built-in Standard PC I/O Ports
- CE, FCC, CCC, BSMI compliant
- Carrying case for easy travel

For PWS-1419T/TP only

- Impact-resistance protective glass for LCD
- Complete aluminum enclosure

Introduction

PWS-1419T/TP Ruggedized Portable Workstation

The PWS-1419 complies with stringent industrial standards. Built with an all aluminum enclosure that has a hard anodized surface, the PWS-1419T/TP has been thoroughly tested and certified to withstand the most demanding environments. The PWS-1419 is dustproof, moisture resistant, shock/drop proof, and heat/cold resistant. Built-in sound and standard PC I/O ports are provided along with a 14.1" TFT LCD with 1024 x 768 resolution.

Its compact size makes it an ideal solution for field operations and it is extremely mobile with the ability to be carried on to a plane or easily fitted into a vehicle. It is ruggedly built and expandable, while meeting MIL-STD-810E military standards and industrial requirements.

PWS-1409T/TP Portable Workstation

The PWS-1409T/TP is a light version of PWS-1419 Portable Workstation, making it also ideal for rugged field and mobile applications. The product is built on an aluminum chassis surrounded by a highly durable ABS plastic shell. It offers a cost effective solution for applications such as portable servers, network/communications testing, field data acquisition, remote field service, factory monitoring automation, etc.

Specifications

- **Backplane** TP version-1 CPU, 4 ISA, 4 PCI
T version-1 CPU, 8 ISA
- **Chassis** PWS-1419 - complete aluminum
PWS-1409 - aluminum chassis w/ABS plastic shell
- **Dimensions (WxHxD)** PWS-1419: 421 x 282 x 230 mm (16.6" x 11.1" x 9.1")
PWS-1409: 400 x 320 x 200 mm (15.7" x 13.2" x 10.4")
- **Keyboard** Full size mechanical key-switch, detachable
- **Power Supply** AC 110/220 V auto switch
- **Storage Device** FDD built-in, plus 1 hard disk bay and 1 slim type CD-ROM bay

Environment

- **Humidity** PWS-1419 5 ~ 95 % RH, non-condensing
PWS-1409 10 ~ 90 % RH, non-condensing
- **Operating Temperature** -8 ~ 60° C
- **Storage Temperature** -20 ~ 60° C
- **Weight** PWS-1419: 12 kg (26.4 lb)
PWS-1409: 9 kg (19.8 lb)

LCD Display


	PWS-1409	PWS-1419
Display Type	14"1 Active Matrix TFT	14"1 Active Matrix TFT
Max. Resolution	1024 x 768	1024 x 768
Max. Colors	262 K	262 K
Viewing Angle	H: left side 40°, right side 40° V: up side 15°, down side 30°	H: left side 50°, right side 50° V: up side 20°, down side 35°
Luminance	130 cd/m ²	130 cd/m ²
Backlight Lifetime	25,000 hrs	25,000 hrs

Ordering Information

- **PWS-1419T** 14.1" LCD, Aluminum Chassis, 8ISA/1CPU, Slim Type FDD
- **PWS-1419TP** 14.1" LCD, Aluminum Chassis, 4ISA/4PCI/1CPU, Slim Type FDD
- **PWS-1409T** 14.1" LCD, Aluminum Chassis w/ ABS Plastic Shell, 8ISA/1CPU, standard type FDD
- **PWS-1409TP** 14.1" LCD Aluminum Chassis w/ ABS Plastic Shell, 4 ISA/4 PCI/1 CPU, standard type FDD


Dimensions

Unit: mm



Dimensions

Unit: mm



Front View

