


- LEAD FREE
- PLATING:
 - 1:GOLD FLASH ALL OVER
 - 4:0.25um(10U")GOLD AT CONTACT
 - 8:0.76um(30U")GOLD AT CONTACT
 - 9:1u" GOLD OVER 30u" PdNi AT CONTACT
- PACKING
- T: TUBE
- PIN COUNT
- SEE TABLE 1

DASH No.	Dim.	Amount of Pins	Dim.A	Dim.B
-000 34 XX LF		34	20.32	27.89
-000 40 XX LF		40	24.13	31.70
-000 44 XX LF		44	26.67	34.24
-000 50 XX LF		50	30.48	38.05
-000 60 XX LF		60	36.83	44.40
-000 64 XX LF		64	39.37	46.94
-000 68 XX LF		68	41.91	49.48
-000 80 XX LF		80	49.53	57.10
-000 A0 XX LF		100	62.23	69.80

Recommended P.C.B. Layout
Layout Tolerance = ± 0.05 mm

mat'l. code				surface ☒ tolerance		product family	
				ISO1302 ☒ ISO1101 ISO406		MINITEK	
ltr ecn nodr date				tolerances unless otherwise specified		title	
A	T09-1117	S.LIN	09/15/09	angle line 0°±2'	0.X±0.38		1.27X1.27MM BTB HEADER SHROUDED VERTICAL TH
B	T10--0022	S.LIN	01/20/10		0.XX±0.25		
C	BLX-N-010362	ZK	01/16/12		0.XXX±0.10		
				scale 5:1			
				dr STERLING LIN 09/15/09		dwg no sheet 1 of 1 size	
				engr STERLING LIN 09/15/09		20021511 A4	
				chr GRAY HSIEH 0915/09			
				appd JOSEPH 09/15/09		type Product Customer Drawing	
sheet index		revisionc sheet 1					