


LOC		DIST		REV		REVISIONS		DATE		APPRO	
6	14	P	F	ZONE	LTR	DESCRIPTION		DATE		APPRO	
				B		REV, RDRW, & SM PKG PER 0720-0040-93		2-24-93		18 DAP	

METRIC
DIMENSIONS LISTED IN mm [INCHES]

AMP WIRE RANGE	IL E13288 Listed
26-22 AWG SOLID OR STRANDED	NOT LISTED
LR7189 Certified	MILITARY P/N AND CLASS
NOT CERTIFIED	NOT APPLICABLE

- 1 STAMP AMP APPROX AS SHOWN
2 MAXIMUM LENGTH DOES NOT INCLUDE
MANUFACTURING TABS



AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111
FOR ORDER ENTRY	1-800-526-5142

MAX RECOMMENDED OPERATING
TEMPERATURE:
170°C MAX

VOLTAGE RATING:
NOT APPLICABLE

WIRE CROSS SECTIONAL AREA RANGE:
0.1-0.41mm² [202-810] CIR MILS

SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN mm [INCHES]
TOLERANCES ON:
2 PLG DEC ±
3 PLG DEC ±
ANGLES ±

DR 2-24-93
TA BRINKMAN
CHK 2-24-93
DA PATTERSON
APPD 2-24-93
DE MILLER
APPD 2-24-93
JL MECKLEY
PRODUCT SPEC
-
APPLICATION SPEC
-
WEIGHT -

NAME
AMP
AMP Incorporated
Harrisburg, PA 17105-3608

SPLICE, BUTT,
STRAP, SOLISTRAND™

SIZE
CAGE CODE
DRAWING NO
00779
321198

SCALE 10:1
SHEET 1 OF 1

100	LOOSE PIECE, BOX	8-321198-1
----	LOOSE PIECE	321198
QUANTITY	PACKAGE TYPE	PART NO