

## Heavy-Duty Computer Power Extension Cord for Servers and Computers, 20A, 12AWG (IEC-320-C19 to Left Angle IEC-320-C20), 2-ft.

MODEL NUMBER: **P036-002-20LA**



### Highlights

- C19 to C20 Left Angle Exit Power Cable, 2 ft.
- 12AWG (3.31mm<sup>2</sup>) x 3C, 20 Amp Rated, 100-250V
- RoHS Approved

### Package Includes

- C19 to C20 Left Angle Power Cable, 2 ft.

### Description

Use Tripp Lite's P036-002-20LA in server applications that require a higher rated, heavier gauge cable, as well as situations where left angle cable exit is required. C19 to C20 connectors, 3 x 12ga (3.31mm<sup>2</sup>) conductors, 20AMP rated, 250V - ideal for use with Blade Server Chassis.

### Features

- Molded, Heavy-Duty Power Cable, 2 ft.
- IEC-60320-C19 to IEC-60320-C20, with Left Angle exit
- 12AWG (3.31mm<sup>2</sup>) x 3C, SJTW, 20A, 250Volt
- RoHS Approved

## Specifications

General Info	
Product Group	POWER CORDS
OVERVIEW	
Intended Application	Powering Devices
Cable Type	POWER
Model Type	Power Cords
INPUT	
Cable Length (ft.)	2



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Cable Length (m)	0.61
<b>UPC ASSIGNMENT</b>	
Unit Carton UPC#	037332156525
<b>PHYSICAL</b>	
Color	Black
Style	Power Cables
<b>CONNECTIONS</b>	
Connector A	IEC-320-C20 - LEFT ANGLE
Connector B	IEC-320-C19
Number of Connectors	2
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.