


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0190010006](#)
Status: **Active**
Description: Avikrimp™ Quick Disconnect, Male, for 14-16 (2.00-1.30), Box, Tab 6.35mm (.250") x 0.81mm (.032")

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Quick Disconnects
Series	19001
Product Name	Avikrimp™
Type	Quick Disconnect
Physical	
Barrel Type	Closed
Flammability	94V-0
Gender	Male
Glow-Wire Compliant	No
Insulation	Nylon (PA)
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Zinc Chromate
Material - Plating Termination	Zinc Chromate
Orientation	Straight
Packaging Type	Bag
Plating min: Mating (µin)	200
Plating min: Mating (µm)	5
Plating min: Termination (µin)	200
Plating min: Termination (µm)	5
Polarized to Mating Part	No
Tab Thickness	0.81mm (.032")
Tab Width	6.35mm (.250")
Temperature Range - Operating	-65°C to +105°C
Wire Insulation Diameter	4.32mm (.170") max.
Wire Size AWG	14
Wire Size AWG	16
Wire Size mm²	1.30 - 2.00
Electrical	
CSA	LR18689
TUV	R9071070
UL	E79133
Voltage - Maximum	300V
Material Info	
Old Part Number	BB-5262
Reference - Drawing Numbers	
Sales Drawing	SD-19001-003



Series image - Reference only

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Halogen-Free
Status
Halogen-Free



Need more information on product environmental compliance?
Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[19001](#) Series

Use With
[19002-0024](#) , [19002-0025](#) , [19002-0027](#)

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.
Global

Description	Product #
Hand Crimp Tool	0640012600
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640052600

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION