





CONNECTOR SPECIFICATION:

VOLTAGE RATING	250 VAC/VDC
AMPERAGE RATING	max. 4 AMPS
PROTECTION	IP67
OPERATING TEMPERATURE	-20°C TO 105°C
UL CERTIFICATIONS	UL RECOGNIZED, FILE NO. E152210
ASSEMBLY	RoHS COMPLIANT

COMPONENT	MATERIAL	FINISH
LABEL	MYLAR	BLACK/YELLOW
COUPLER	BRASS	NICKEL PLATED
PIN CONTACT	COPPER ALLOY	GOLD OVER NICKEL
INSERT	NYLON	BLACK
OVERMOLD	PUR	YELLOW
CABLE- 22/AWG CONDUCT. 300V	JACKET: PVC	JACKET: YELLOW

803006A09M020

no poles
3-5 pole

cable type
#22/3-5
PVC YELLOW

cable length
020----2 Meters
100----10 Meters

MATERIAL NUMBER	ENGINEERING NUMBER	FINISHED LENGTH
1200650200	803006A09M020	6.56' +3.5" -0 [2.0M +89 -0]
1200650414	804006A09M020	6.56' +3.5" -0 [2.0M +89 -0]
1200650523	805006A09M020	6.56' +3.5" -0 [2.0M +89 -0]
1200650533	805006A09M100	32.81' +12.5" -0 [10.0M +318 -0]

UPDATED FOR PART NUMBER MATRIX EC NO.:IPG2014-0988 DRWN: GGUSTAFS 11/26/13 CHKD: TWOLDEGE APPR: BWOODMAN 2010/01/25 A		DESCRIPTION	REV	QUALITY SYMBOLS ▽ = 0 ▽C = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE IN/MM		SCALE NTS	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION		
						mm	INCH	DRAWN BY DATE GGUSTAFS 2013/11/26		MICRO-CHANGE ASSEMBLY 3-5 POLE MA STR 22/AWG YELLOW PVC CABLE				
					4 PLACES	±---	±---	CHECKED BY DATE RE 2010/01/21						
					3 PLACES	±---	±.005	APPROVED BY DATE NSTAUDIG 2010/01/25						
					2 PLACES	±.13	±.010	MATERIAL NO. SEE CHART						DOCUMENT NO. SD-120065-028
					1 PLACE	±.25	±.020			MOLEX INCORPORATED				
					ANGULAR ± .5 °									
					DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS									
					SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							