





(1.27 mm) .050"

FFMD-20-T-02.00-01-N-R



FFMD-10-S-10.00-01



FFMD SERIES

# TIGER EYE™ FLAT IDC WIRE CABLES

## Mates with:

FLE\*, SFMC\*,

## Transfer End Option

Mates with: FTS, FTSH,  
EHF, SHF, ESHF

## SPECIFICATIONS

For complete specifications  
see [www.samtec.com?FFMD](http://www.samtec.com?FFMD)

### Insulator Material:

Black Glass Filled Polyester

### Terminal:

Phosphor Bronze

### Contact:

BeCu (-T)

### Plating:

Sn over 50µ" (1.27 µm) Ni

### Wire:

30 AWG

### Current Rating:

2.5 A per pin

(1 pin powered)

### Operating Temp Range:

-40°C to +105°C

### Voltage Rating:

215 VAC

304 VDC

### RoHS Compliant:

Yes

## RECOGNITIONS

For complete scope of  
recognitions see  
[www.samtec.com/quality](http://www.samtec.com/quality)


FILE NO. E111594

## ALSO AVAILABLE (MOQ Required)

- Other sizes
- Contact Samtec.

**\*Note:** Standard FFMD callout  
will not mate with FLE, SFMC.  
Must use gold plated callouts.  
(See drawing on web.)  
When mated with a socket,  
Wire 1 mates with Pin 2;  
Wire 2 mates with Pin 1, etc.

**Note:** This Series is  
non-standard, non-returnable.



## FFMD = Terminal Strip

