

## Industrial Adhesives & Tapes

[Products](#) | [Applications](#) | [Industries](#) | [Capabilities](#) | [Support](#)[Where to Buy](#)

United States > All 3M Products > Market Segments > Manufacturing and Industry > Industrial Adhesives & Tapes > Industrial Adhesives & Tapes > Fasteners & Gripping Material > 3M™ Dual Lock™ Reclosable Fasteners > 3M™ Dual Lock™ Reclosable Fastener SJ3560 250 Clear, 1/2 in x 50 yd 0.23 in (5.8 mm), 4 per case Bulk

# 3M™ Dual Lock™ Reclosable Fastener SJ3560 250 Clear, 1/2 in x 50 yd 0.23 in (5.8 mm), 4 per case Bulk

UPC# 00021200862809 3M Product Number SJ3560 3M ID 70070428365



A clear acrylic adhesive on the back of a clear polypropylene reclosable fastener. 250 stems per square inch. 0.23 inch engaged thickness. Closure life 1,000.

- A clear fastener with mushroom shaped stems backed with a clear, acrylic pressure sensitive adhesive.
- Type 250 stem density polyolefin fastener which mates to Type 170, 250 or 400.
- Designed to bond to metals, glass and high surface energy plastics.
- General Industrial, Speciality Vehicles, Transportation, Military, Packaging, Medical, Point of Purchase Displays, Exhibits, Electronics, Construction, Furniture, Maintenance Repair and Operations (MRO).
- Attach Doors, Access Panels, Signs, Cushions, Headliners and Display Components.

[Need Help?](#)

**Questions?** We can help  
[Contact Us](#)

[View All Images](#)

 Network Access Message: The page

[Where to Buy](#)[Overview](#) [Support](#)

For indoor and outdoor use. Highest temperature performance, temperature resistance 220 degrees F. For use with metals (aluminum, stainless steel), glass, and high surface energy plastics (acrylic, polycarbonate, ABS).

## Specifications

Adhesive Type	Clear Acrylic Adhesive
Application	Ceiling Attachment, Panel Attachment Systems, Wood Blinds Trim Attachment
Brand	Dual Lock
Closure Life	1000
Color	Clear
Engaged Thickness	0.23 Inch
Flame Retardant	No
Indoor/Outdoor	Both
Industry - Use	Construction, Electronics, Furniture, General Industrial, Medical, Military & Government, MRO, Packaging, Retail, Specialty Vehicle, Transportation
Length	50 Linear Yard
Length (metric)	45.72 Linear Metre
Liner Thickness	4 Milli-inch (mil)
Liner Type	Clear Polyolefin
Low Profile	No
Maximum Operating Temperature (Fahrenheit)	220 Degree Fahrenheit
Product Form	Roll
Stem Density	250
Units per Case	4
Width	0.50 Inch
Width (metric)	12.70 Millimetre

