







SECTION A-A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN — 19MAR75	TE Connectivity	
DIMENSIONS: INCHES		CHK — 20MAR75		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD — 20MAR75	NAME	
0 PLC ± -		PRODUCT SPEC	HOUSING ASSY, LOW PROFILE, EDGE CONNECTOR, FLOW SOLDER, FOR .052 DIA. HOLE, .156X.200 CENTERS.	
1 PLC ± -		APPLICATION SPEC	SIZE	CAGE CODE
2 PLC ± -		—	A2	00779
3 PLC ± .005		WEIGHT	C=530655	
4 PLC ± -		CUSTOMER DRAWING	RESTRICTED TO	
ANGLES ± -		SCALE	1 of 2	
FINISH		4:1	REV M3	
SEE CALL-OUT				

D

- 1

.000015 MIN GOLD OVER .000050 MIN. NICKEL IN CONTACT AREA.
- 2

.000030 MIN GOLD OVER .00005 MIN. NICKEL IN CONTACT AREA.
- 3

SELECTIVELY LOADED, OMIT CONTACTS IN CIRCUIT CAVITIES
14,16,18,S AND U
- 4

ALL PARTS ASSEMBLED IN MEXICO MUST BE STAMPED "ASSY IN MEXICO"
THE WORD "MEXICO" CAN BE SUBSTITUTED ONLY WHERE PART SIZE
PROHIBTS STAMPING "ASSY IN MEXICO", INK STAMP COLOUR WHITE OR HOT
STAMP (NO WHITE TAPE) 115-9009, APPROX. WHERE SHOWN, SIDE OPTIONAL.
- 5

MATTE TIN PLATED CONTACT TAILS.
- 6

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

D

C

5	-	43	6.552	6.872	7.307	7.012	.437	7.557	6	8-530655-3
5	-	28	4.212	4.532	4.967	4.672	.370	5.217	6	8-530655-2
5	-	36	5.460	5.780	6.215	5.920	.437	6.465	6	8-530655-0
5	-	30	4.524	4.844	5.279	4.984	.437	5.529		7-530655-9
5	-	22	3.276	3.596	4.031	3.736	.370	4.281		7-530655-6
5	-	18	2.652	2.972	3.407	3.112	.370	3.657		7-530655-5
5	-	15	2.184	2.504	2.939	2.644	.370	3.189		7-530655-4
5	-	12	1.716	2.036	2.471	2.176	.370	2.721		7-530655-3
5	-	10	1.404	1.724	2.159	1.864	.370	2.409		7-530655-2
5	-	6	.780	1.100	1.535	1.240	.370	1.785		7-530655-1
	-	18	2.652	2.972	3.407	3.112	.370	3.657		3-530655-4
	1-530655-3	43	6.552	6.872	7.307	7.012	.437	7.557		3-530655-3
	1-530655-2	28	4.212	4.532	4.967	4.672	.370	5.217		3-530655-2
	1-530655-1	44	6.708	7.028	7.463	7.168	.437	7.713		3-530655-1
	1-530655-0	36	5.460	5.780	6.215	5.920	.437	6.465		3-530655-0
	530655-9	30	4.524	4.844	5.279	4.984	.437	5.529	6	2-530655-9
	530655-8	25	3.744	4.064	4.499	4.204	.370	4.749		2-530655-8
	530655-7	24	3.588	3.908	4.343	4.048		4.593		2-530655-7
	530655-6	22	3.276	3.596	4.031	3.736		4.281		2-530655-6
	530655-5	18	2.652	2.972	3.407	3.112		3.657		2-530655-5
	530655-4	15	2.184	2.504	2.939	2.644		3.189		2-530655-4
	530655-3	12	1.716	2.036	2.471	2.176		2.721		2-530655-3
	530655-2	10	1.404	1.724	2.159	1.864		2.409		2-530655-2
	530655-1	6	.780	1.100	1.535	1.240		1.785		2-530655-1
1	PART NO	NO.OF. POSITION	A	B	C	D	W	F	2	PART NO

OBSOLETE

530655

B

B

A

A

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

MATERIAL
SEE CALL-OUT

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH
SEE CALL-OUT

DWN - 19MAR75
CHK - 20MAR75
APVD - 20MAR75

PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT -

CUSTOMER DRAWING

19MAR75
20MAR75
20MAR75

TE Connectivity

HOUSING ASSY, LOW PROFILE,
EDGE CONNECTOR, FLOW SOLDER,
FOR .052 DIA. HOLE .156X.200 CTRS.

SIZE A2
CAGE CODE 00779
DRAWING NO C=530655
RESTRICTED TO -

SCALE 1:1
SHEET 2 of 2
REV M3